

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P205691

Luminaire Tested: **LD4B15D010 EU4B10208030 4LBSH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P205691
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD4B15D010 EU4B10208030 4LBSH1
Description: PORTFOLIO 4 INCH SHALLOW RECESSED DOWNLIGHT
SHALLOW DISTRIBUTION WITH SEMI-SPECULAR CLEAR TRIM
WATTAGE D010TR-14.39W DE010-14.29W D5LT-14.34W DMX-14.46W DL2-15.8W
DL3-15.28W DLE-15.432W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1468.3 lumens
Efficiency: N/A
Efficacy: 102.7 lumens/watt
Spacing Criteria (0/90/45): 1.06 / 1.06 / 1.17
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P205691

CATALOG NUMBER: LD4B15D010 EU4B10208030 4LBSH1

Luminous Intensity Polar Plot





TEST NUMBER: P205691

CATALOG NUMBER: LD4B15D010 EU4B10208030 4LBSH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90	88		
2	102	96	90	85	100	94	88	84	90	86	82	87	83	80	84	81	79	77		
3	95	85	78	73	92	84	77	72	81	75	71	78	74	70	76	72	69	67		
4	87	77	69	63	85	75	68	63	73	67	62	71	65	61	69	64	60	58		
5	81	69	61	55	79	68	61	55	66	60	55	64	59	54	63	58	53	51		
6	75	63	55	49	73	62	54	49	60	54	49	59	53	48	57	52	48	46		
7	70	58	50	44	68	57	49	44	55	49	44	54	48	43	53	47	43	41		
8	65	53	45	40	64	52	45	40	51	44	39	50	44	39	49	43	39	37		
9	61	49	41	36	60	48	41	36	47	40	36	46	40	36	45	40	35	34		
10	58	45	38	33	56	45	38	33	44	37	33	43	37	33	42	37	33	31		

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P205691

CATALOG NUMBER: LD4B15D010 EU4B10208030 4LBSH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	71.9	4.9
10°-20°	195.5	13.3
20°-30°	271.5	18.5
30°-40°	296.3	20.2
40°-50°	276.4	18.8
50°-60°	209.8	14.3
60°-70°	114.9	7.8
70°-80°	31.6	2.2
80°-90°	0.4	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	538.9	36.7
0°-40°	835.2	56.9
0°-60°	1321.4	90.0
0°-90°	1468.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1468.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	768	
5°	761	72
15°	697	196
25°	590	272
35°	474	296
45°	359	276
55°	234	210
65°	115	115
75°	28	32
85°	0	0
90°	0	



TEST NUMBER: P205691

CATALOG NUMBER: LD4B15D010 EU4B10208030 4LBSH1

CANDELA DISTRIBUTION (FULL):

	0°
0°	767.9
2.5°	767.9
5°	761.4
7.5°	751.7
10°	737.2
12.5°	717.8
15°	696.8
17.5°	670.9
20°	646.7
22.5°	617.6
25°	590.1
27.5°	562.6
30°	531.9
32.5°	502.8
35°	473.7
37.5°	444.6
40°	417.1
42.5°	388.0
45°	358.9
47.5°	329.8
50°	297.5
52.5°	266.7
55°	234.4
57.5°	203.7
60°	173.0
62.5°	142.3
65°	114.8
67.5°	88.9
70°	66.3
72.5°	45.3
75°	27.5
77.5°	12.9
80°	3.2
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)