

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P206321

Luminaire Tested: **LD4B15D010 EU4B10209030 4LBCSMW1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P206321
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD4B15D010 EU4B10209030 4LBSCMW1
Description: PORTFOLIO 4 INCH SHALLOW RECESSED DOWNLIGHT
SHALLOW DISTRIBUTION WITH CAST MATTE WHITE TRIM
WATTAGE D010TR-14.39W DE010-14.29W D5LT-14.34W DMX-14.46W DL2-15.8W
DL3-15.28W DLE-15.432W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1332.8 lumens
Efficiency: N/A
Efficacy: 93.2 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.23 / 1.33
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P206321

CATALOG NUMBER: LD4B15D010 EU4B10209030 4LBCSMW1

Luminous Intensity Polar Plot





TEST NUMBER: P206321

CATALOG NUMBER: LD4B15D010 EU4B10209030 4LBCSMW1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	110	106	102	99	108	104	100	97	100	97	94		96	93	91		92
2	101	94	87	82	99	92	86	81	88	84	79		85	81	78		82
3	93	83	75	70	90	81	74	69	79	73	68		76	71	67		73
4	85	74	66	60	83	73	65	59	70	64	58		68	62	58		66
5	79	66	58	52	77	65	57	51	63	56	51		61	55	50		60
6	73	60	52	45	71	59	51	45	57	50	45		56	49	44		54
7	68	55	46	40	66	54	46	40	52	45	40		51	44	40		50
8	63	50	42	36	61	49	41	36	48	41	36		47	40	36		46
9	59	46	38	33	57	45	38	32	44	37	32		43	37	32		42
10	55	42	35	30	54	42	34	30	41	34	29		40	34	29		39

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P206321

CATALOG NUMBER: LD4B15D010 EU4B10209030 4LBCSMW1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	51.6	3.9
10°-20°	146.8	11.0
20°-30°	220.9	16.6
30°-40°	261.8	19.6
40°-50°	260.5	19.5
50°-60°	210.0	15.8
60°-70°	127.1	9.5
70°-80°	47.2	3.5
80°-90°	7.0	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	419.3	31.5
0°-40°	681.1	51.1
0°-60°	1151.5	86.4
0°-90°	1332.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1332.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	544	
5°	542	52
15°	520	147
25°	480	221
35°	419	262
45°	339	260
55°	234	210
65°	128	127
75°	43	47
85°	6	7
90°	0	



TEST NUMBER: P206321

CATALOG NUMBER: LD4B15D010 EU4B10209030 4LBSCMW1

CANDELA DISTRIBUTION (FULL):

0°	
0°	544.3
2.5°	544.3
5°	541.9
7.5°	540.3
10°	535.5
12.5°	527.4
15°	520.1
17.5°	512.0
20°	502.4
22.5°	492.7
25°	479.7
27.5°	466.0
30°	450.7
32.5°	436.1
35°	419.2
37.5°	401.4
40°	380.4
42.5°	360.2
45°	339.2
47.5°	315.8
50°	289.9
52.5°	263.3
55°	234.2
57.5°	208.4
60°	179.3
62.5°	153.5
65°	127.6
67.5°	103.4
70°	80.8
72.5°	60.6
75°	42.8
77.5°	27.5
80°	16.2
82.5°	9.7
85°	5.7
87.5°	2.4
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)