

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P207363

Luminaire Tested: **LD4B20D010 EU4B10209027 4LBMGPH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P207363
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD4B20D010 EU4B10209027 4LBMGPH1
Description: PORTFOLIO 4 INCH 50 DEGREE CUTOFF RECESSED DOWNLIGHT
MEDIUM DISTRIBUTION WITH GRAPHITE HAZE TRIM
WATTAGE D010TR-21.86W DE010-20.46W D5LT-21.24W DMX-20.89W DL2-22.5W
DL3-21.8 6W DLE-22.46W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 897.8 lumens
Efficiency: N/A
Efficacy: 43.2 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 0.92
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 20.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P207363

CATALOG NUMBER: LD4B20D010 EU4B10209027 4LBMGPH1

Luminous Intensity Polar Plot





TEST NUMBER: P207363

CATALOG NUMBER: LD4B20D010 EU4B10209027 4LBMGPH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	108	105	111	108	106	104	104	102	101		100	99	98		97
2	107	102	98	94	105	100	97	93	97	94	91		94	92	89		91
3	102	95	90	85	100	93	89	85	91	87	83		88	85	82		86
4	96	88	82	78	94	87	82	78	85	80	77		83	79	76		81
5	91	82	76	72	89	81	76	71	79	74	71		78	73	70		76
6	86	77	71	66	85	76	70	66	74	69	65		73	68	65		72
7	82	72	66	61	80	71	65	61	70	65	61		69	64	60		68
8	77	67	61	57	76	67	61	57	66	60	57		65	60	56		64
9	73	63	57	53	72	63	57	53	62	57	53		61	56	53		60
10	70	60	54	50	69	59	54	50	59	53	50		58	53	49		57

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P207363

CATALOG NUMBER: LD4B20D010 EU4B10209027 4LBMGPH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	84.9	9.5
10°-20°	221.5	24.7
20°-30°	284.1	31.6
30°-40°	205.3	22.9
40°-50°	73.6	8.2
50°-60°	19.9	2.2
60°-70°	6.5	0.7
70°-80°	2.0	0.2
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	590.5	65.8
0°-40°	795.8	88.6
0°-60°	889.3	99.1
0°-90°	897.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	897.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	923	
5°	906	85
15°	789	221
25°	627	284
35°	328	205
45°	89	74
55°	21	20
65°	6	7
75°	2	2
85°	0	0
90°	0	



TEST NUMBER: P207363

CATALOG NUMBER: LD4B20D010 EU4B10209027 4LBMGPH1

CANDELA DISTRIBUTION (FULL):

0°	
0°	923.0
2.5°	919.2
5°	906.0
7.5°	885.3
10°	857.0
12.5°	824.9
15°	789.0
17.5°	753.1
20°	717.3
22.5°	675.8
25°	626.7
27.5°	570.0
30°	498.3
32.5°	415.3
35°	328.4
37.5°	249.2
40°	181.2
42.5°	128.4
45°	88.7
47.5°	60.4
50°	39.6
52.5°	28.3
55°	20.8
57.5°	15.1
60°	11.3
62.5°	9.4
65°	5.7
67.5°	3.8
70°	3.8
72.5°	1.9
75°	1.9
77.5°	1.9
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)