

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P207660

Luminaire Tested: **LD4B15D010 EU4B10209030 4LBNH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P207660
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD4B15D010 EU4B10209030 4LBNH1
Description: PORTFOLIO 4 INCH 50 DEGREE CUTOFF RECESSED DOWNLIGHT
NARROW DISTRIBUTION WITH SEMI-SPECULAR CLEAR TRIM
WATTAGE D010TR-14.39W DE010-14.29W D5LT-14.34W DMX-14.46W DL2-15.8W
DL3-15.28W DLE-15.432W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 798.2 lumens
Efficiency: N/A
Efficacy: 55.8 lumens/watt
Spacing Criteria (0/90/45): 0.81 / 0.81 / 0.85
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P207660

CATALOG NUMBER: LD4B15D010 EU4B10209030 4LBNH1

Luminous Intensity Polar Plot





TEST NUMBER: P207660

CATALOG NUMBER: LD4B15D010 EU4B10209030 4LBNH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	111	108	106	111	109	106	104	105	103	101		101	99	98		97
2	108	103	99	96	106	101	98	94	98	95	92		95	93	90		92
3	102	96	91	87	100	95	90	86	92	88	85		90	86	84		87
4	97	90	84	80	95	89	83	79	86	82	79		84	81	78		83
5	92	84	78	74	91	83	78	73	81	76	73		80	75	72		78
6	88	79	73	69	86	78	72	68	77	72	68		75	71	67		74
7	83	74	68	64	82	73	68	64	72	67	63		71	66	63		70
8	79	70	64	60	78	69	64	60	68	63	59		67	63	59		66
9	76	66	60	56	74	65	60	56	65	59	56		64	59	56		63
10	72	62	57	53	71	62	56	53	61	56	53		60	56	52		60

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P207660

CATALOG NUMBER: LD4B15D010 EU4B10209030 4LBNH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	90.4	11.3
10°-20°	219.4	27.5
20°-30°	254.6	31.9
30°-40°	168.6	21.1
40°-50°	47.3	5.9
50°-60°	11.9	1.5
60°-70°	4.4	0.6
70°-80°	1.5	0.2
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	564.4	70.7
0°-40°	733.1	91.8
0°-60°	792.2	99.3
0°-90°	798.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	798.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1002	
5°	976	90
15°	785	219
25°	558	255
35°	270	169
45°	55	47
55°	13	12
65°	4	4
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P207660

CATALOG NUMBER: LD4B15D010 EU4B10209030 4LBNH1

CANDELA DISTRIBUTION (FULL):

	0°
0°	1002.2
2.5°	997.9
5°	976.2
7.5°	938.6
10°	892.3
12.5°	840.3
15°	785.3
17.5°	731.8
20°	672.5
22.5°	617.5
25°	558.2
27.5°	501.8
30°	429.5
32.5°	352.9
35°	270.4
37.5°	193.8
40°	131.6
42.5°	85.3
45°	55.0
47.5°	33.3
50°	21.7
52.5°	15.9
55°	13.0
57.5°	10.1
60°	7.2
62.5°	5.8
65°	4.3
67.5°	2.9
70°	2.9
72.5°	1.4
75°	1.4
77.5°	1.4
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)