

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P207054

Luminaire Tested: **LD4B20D010 EU4B10209027 4LBWMW1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P207054
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD4B20D010 EU4B10209027 4LBWMW1
Description: PORTFOLIO 4 INCH 60 DEGREE CUTOFF RECESSED DOWNLIGHT
WIDE DISTRIBUTION WITH MATTE WHITE TRIM
WATTAGE D010TR-21.86W DE010-20.46W D5LT-21.24W DMX-20.89W DL2-22.5W
DL3-21.8 6W DLE-22.46W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1452.4 lumens
Efficiency: N/A
Efficacy: 69.8 lumens/watt
Spacing Criteria (0/90/45): 1.1 / 1.1 / 1.09
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 20.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P207054

CATALOG NUMBER: LD4B20D010 EU4B10209027 4LBWMW1

Luminous Intensity Polar Plot






TEST NUMBER: P207054

CATALOG NUMBER: LD4B20D010 EU4B10209027 4LBWMW1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	111	107	104	101	108	105	102	99	101	98	96		97	95	93		93
2	103	96	91	86	101	94	89	85	91	87	83		88	84	81		85
3	96	87	80	75	93	85	79	74	83	77	73		80	76	72		78
4	89	79	72	66	87	78	71	66	75	69	65		73	68	64		71
5	83	72	64	59	81	71	64	58	69	63	58		67	62	57		65
6	78	66	58	53	76	65	58	53	64	57	52		62	56	52		60
7	73	61	53	48	71	60	53	48	59	52	47		57	51	47		56
8	68	56	49	44	67	56	49	44	54	48	43		53	47	43		52
9	64	52	45	40	63	52	45	40	51	44	40		50	44	40		49
10	61	49	42	37	59	48	41	37	47	41	37		46	41	37		46

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P207054

CATALOG NUMBER: LD4B20D010 EU4B10209027 4LBWMW1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	82.6	5.7
10°-20°	231.1	15.9
20°-30°	326.6	22.5
30°-40°	316.3	21.8
40°-50°	213.5	14.7
50°-60°	132.5	9.1
60°-70°	88.6	6.1
70°-80°	48.4	3.3
80°-90°	12.8	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	640.3	44.1
0°-40°	956.6	65.9
0°-60°	1302.6	89.7
0°-90°	1452.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1452.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	880	
5°	873	83
15°	820	231
25°	716	327
35°	509	316
45°	273	213
55°	145	132
65°	89	89
75°	45	48
85°	11	13
90°	0	



TEST NUMBER: P207054

CATALOG NUMBER: LD4B20D010 EU4B10209027 4LBWMW1

CANDELA DISTRIBUTION (FULL):

	0°
0°	880.1
2.5°	880.1
5°	872.6
7.5°	863.1
10°	851.8
12.5°	840.5
15°	819.8
17.5°	802.8
20°	774.6
22.5°	746.3
25°	716.1
27.5°	674.7
30°	629.4
32.5°	571.0
35°	508.8
37.5°	446.6
40°	384.5
42.5°	322.3
45°	273.3
47.5°	228.0
50°	194.1
52.5°	165.8
55°	145.1
57.5°	128.2
60°	115.0
62.5°	101.8
65°	88.6
67.5°	77.3
70°	66.0
72.5°	56.5
75°	45.2
77.5°	35.8
80°	26.4
82.5°	18.8
85°	11.3
87.5°	3.8
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)