

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P207150

Luminaire Tested: **LD4B15D010 EU4B10209730 4LBMH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P207150
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD4B15D010 EU4B10209730 4LBMH1
Description: PORTFOLIO 4 INCH 50 DEGREE CUTOFF RECESSED DOWNLIGHT
MEDIUM DISTRIBUTION WITH SEMI-SPECULAR CLEAR TRIM
WATTAGE D010TR-14.39W DE010-14.29W D5LT-14.34W DMX-14.46W DL2-15.8W
DL3-15.28W DLE-15.432W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 839.1 lumens
Efficiency: N/A
Efficacy: 58.7 lumens/watt
Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.93
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P207150

CATALOG NUMBER: LD4B15D010 EU4B10209730 4LBMH1

Luminous Intensity Polar Plot





TEST NUMBER: P207150

CATALOG NUMBER: LD4B15D010 EU4B10209730 4LBMH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	108	105	111	108	106	104	104	102	100		100	99	97		97
2	107	102	98	94	105	100	96	93	97	94	91		94	91	89		91
3	101	94	89	85	99	93	88	84	90	86	83		88	84	82		86
4	96	88	82	77	94	86	81	77	84	80	76		82	78	75		80
5	90	82	75	71	89	81	75	70	79	74	70		77	73	69		75
6	86	76	70	65	84	75	69	65	74	68	64		72	68	64		71
7	81	71	65	60	80	70	64	60	69	64	60		68	63	59		67
8	77	67	60	56	75	66	60	56	65	59	56		64	59	55		63
9	73	63	56	52	72	62	56	52	61	56	52		60	55	52		59
10	69	59	53	49	68	59	53	49	58	52	49		57	52	48		56

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P207150

CATALOG NUMBER: LD4B15D010 EU4B10209730 4LBMH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	76.6	9.1
10°-20°	200.8	23.9
20°-30°	258.1	30.8
30°-40°	194.2	23.1
40°-50°	78.0	9.3
50°-60°	22.2	2.6
60°-70°	7.0	0.8
70°-80°	2.0	0.2
80°-90°	0.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	535.5	63.8
0°-40°	729.7	87.0
0°-60°	829.9	98.9
0°-90°	839.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	839.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	832	
5°	817	77
15°	717	201
25°	570	258
35°	312	194
45°	96	78
55°	23	22
65°	6	7
75°	1	2
85°	0	0
90°	0	



TEST NUMBER: P207150

CATALOG NUMBER: LD4B15D010 EU4B10209730 4LBMH1

CANDELA DISTRIBUTION (FULL):

	0°
0°	832.0
2.5°	826.9
5°	816.8
7.5°	797.8
10°	773.8
12.5°	744.6
15°	716.8
17.5°	685.1
20°	650.9
22.5°	614.2
25°	569.9
27.5°	516.7
30°	454.6
32.5°	385.0
35°	311.5
37.5°	243.1
40°	182.4
42.5°	134.2
45°	96.2
47.5°	65.9
50°	45.6
52.5°	31.7
55°	22.8
57.5°	16.5
60°	12.7
62.5°	8.9
65°	6.3
67.5°	5.1
70°	3.8
72.5°	2.5
75°	1.3
77.5°	1.3
80°	1.3
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)