

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P207871

Luminaire Tested: **LD4B15D010 EU4B10209730 4LBNB1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P207871  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LD4B15D010 EU4B10209730 4LBNB1  
Description: PORTFOLIO 4 INCH 50 DEGREE CUTOFF RECESSED DOWNLIGHT  
NARROW DISTRIBUTION WITH SPECULAR BLACK TRIM  
WATTAGE D010TR-14.39W DE010-14.29W D5LT-14.34W DMX-14.46W DL2-15.8W  
DL3-15.28W DLE-15.432W  
Light Source: HIGH LUMEN LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 432.8 lumens  
Efficiency: N/A  
Efficacy: 30.3 lumens/watt  
Spacing Criteria (0/90/45): 0.62 / 0.62 / 0.79  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 14.3  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P207871

CATALOG NUMBER: LD4B15D010 EU4B10209730 4LBNB1

### Luminous Intensity Polar Plot






TEST NUMBER: P207871

CATALOG NUMBER: LD4B15D010 EU4B10209730 4LBNB1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |  |     |     |     |  |  |     |     |     |  |  |     |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|--|-----|-----|-----|--|--|-----|-----|-----|--|--|-----|
| RF  | 20  |     |     |     | 20  |     |     |     |  | 20  |     |     |  |  | 20  |     |     |  |  | 20  |
| RC  | 80  |     |     |     | 70  |     |     |     |  | 50  |     |     |  |  | 30  |     |     |  |  | 10  |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  |  | 50  | 30  | 10  |  |  | 50  | 30  | 10  |  |  | 50  |
| RCR |     |     |     |     |     |     |     |     |  |     |     |     |  |  |     |     |     |  |  |     |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 |  | 111 | 111 | 111 |  |  | 106 | 106 | 106 |  |  | 102 |
| 1   | 114 | 111 | 109 | 107 | 111 | 109 | 107 | 105 |  | 105 | 103 | 102 |  |  | 101 | 100 | 99  |  |  | 98  |
| 2   | 109 | 104 | 100 | 97  | 106 | 102 | 99  | 96  |  | 99  | 96  | 94  |  |  | 96  | 94  | 92  |  |  | 93  |
| 3   | 104 | 98  | 93  | 89  | 102 | 96  | 92  | 88  |  | 94  | 90  | 87  |  |  | 91  | 88  | 86  |  |  | 89  |
| 4   | 99  | 92  | 86  | 82  | 97  | 90  | 86  | 82  |  | 88  | 84  | 81  |  |  | 86  | 83  | 80  |  |  | 85  |
| 5   | 94  | 86  | 81  | 77  | 92  | 85  | 80  | 76  |  | 84  | 79  | 76  |  |  | 82  | 78  | 75  |  |  | 80  |
| 6   | 90  | 81  | 76  | 72  | 88  | 81  | 75  | 71  |  | 79  | 74  | 71  |  |  | 78  | 74  | 70  |  |  | 76  |
| 7   | 86  | 77  | 71  | 67  | 84  | 76  | 71  | 67  |  | 75  | 70  | 67  |  |  | 74  | 69  | 66  |  |  | 73  |
| 8   | 82  | 73  | 67  | 63  | 80  | 72  | 67  | 63  |  | 71  | 66  | 63  |  |  | 70  | 66  | 62  |  |  | 69  |
| 9   | 78  | 69  | 63  | 60  | 77  | 68  | 63  | 59  |  | 67  | 63  | 59  |  |  | 67  | 62  | 59  |  |  | 66  |
| 10  | 75  | 65  | 60  | 56  | 74  | 65  | 60  | 56  |  | 64  | 59  | 56  |  |  | 63  | 59  | 56  |  |  | 63  |

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P207871

CATALOG NUMBER: LD4B15D010 EU4B10209730 4LBNB1

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 59.0   | 13.6      |
| 10°-20°   | 125.1  | 28.9      |
| 20°-30°   | 145.1  | 33.5      |
| 30°-40°   | 90.9   | 21.0      |
| 40°-50°   | 12.8   | 3.0       |
| 50°-60°   | 0.0    | 0.0       |
| 60°-70°   | 0.0    | 0.0       |
| 70°-80°   | 0.0    | 0.0       |
| 80°-90°   | 0.0    | 0.0       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-30°    | 329.2  | 76.0      |
| 0°-40°    | 420.0  | 97.0      |
| 0°-60°    | 432.8  | 100.0     |
| 0°-90°    | 432.8  | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 432.8  | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°  | Flux |
|-----|-----|------|
| 0°  | 708 |      |
| 5°  | 656 | 59   |
| 15° | 444 | 125  |
| 25° | 320 | 145  |
| 35° | 146 | 91   |
| 45° | 11  | 13   |
| 55° | 0   | 0    |
| 65° | 0   | 0    |
| 75° | 0   | 0    |
| 85° | 0   | 0    |
| 90° | 0   |      |



TEST NUMBER: P207871

CATALOG NUMBER: LD4B15D010 EU4B10209730 4LBNB1

**CANDELA DISTRIBUTION (FULL):**

|       | 0°    |
|-------|-------|
| 0°    | 707.7 |
| 2.5°  | 693.8 |
| 5°    | 655.8 |
| 7.5°  | 601.4 |
| 10°   | 545.7 |
| 12.5° | 492.5 |
| 15°   | 444.4 |
| 17.5° | 403.9 |
| 20°   | 373.5 |
| 22.5° | 345.6 |
| 25°   | 320.3 |
| 27.5° | 289.9 |
| 30°   | 250.7 |
| 32.5° | 201.3 |
| 35°   | 145.6 |
| 37.5° | 95.0  |
| 40°   | 54.4  |
| 42.5° | 27.9  |
| 45°   | 11.4  |
| 47.5° | 2.5   |
| 50°   | 0.0   |
| 52.5° | 0.0   |
| 55°   | 0.0   |
| 57.5° | 0.0   |
| 60°   | 0.0   |
| 62.5° | 0.0   |
| 65°   | 0.0   |
| 67.5° | 0.0   |
| 70°   | 0.0   |
| 72.5° | 0.0   |
| 75°   | 0.0   |
| 77.5° | 0.0   |
| 80°   | 0.0   |
| 82.5° | 0.0   |
| 85°   | 0.0   |
| 87.5° | 0.0   |
| 90°   | 0.0   |



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)