

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P206234

Luminaire Tested: **LD4B20D010 EU4B10209727 4LBPSMW1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P206234
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD4B20D010 EU4B10209727 4LBPSMW1
Description: PORTFOLIO 4 INCH SHALLOW RECESSED DOWNLIGHT
SHALLOW DISTRIBUTION WITH PLASTIC MATTE WHITE TRIM
WATTAGE D010TR-21.86W DE010-20.46W D5LT-21.24W DMX-20.89W DL2-22.5W
DL3-21.8 6W DLE-22.46W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1542.2 lumens
Efficiency: N/A
Efficacy: 74.1 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.24 / 1.34
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 20.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P206234

CATALOG NUMBER: LD4B20D010 EU4B10209727 4LBPSMW1

Luminous Intensity Polar Plot





TEST NUMBER: P206234

CATALOG NUMBER: LD4B20D010 EU4B10209727 4LBPSMW1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	110	106	102	99	107	104	100	97	99	97	94	96	93	91	92	90	88	86		
2	101	93	87	82	98	92	86	81	88	83	79	85	81	77	82	79	76	74		
3	93	83	75	69	90	81	74	69	78	72	67	76	70	66	73	69	65	63		
4	85	74	65	59	83	72	65	59	70	63	58	68	62	57	66	61	56	54		
5	78	66	58	51	76	65	57	51	63	56	51	61	55	50	59	54	49	47		
6	73	60	51	45	71	59	51	45	57	50	44	55	49	44	54	48	44	42		
7	67	54	46	40	66	54	46	40	52	45	40	51	44	39	49	43	39	37		
8	63	50	41	36	61	49	41	36	48	41	35	46	40	35	45	39	35	33		
9	59	46	38	32	57	45	37	32	44	37	32	43	36	32	42	36	32	30		
10	55	42	34	29	54	42	34	29	41	34	29	40	33	29	39	33	29	27		

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P206234

CATALOG NUMBER: LD4B20D010 EU4B10209727 4LBPSMW1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	58.9	3.8
10°-20°	167.8	10.9
20°-30°	252.7	16.4
30°-40°	300.7	19.5
40°-50°	300.2	19.5
50°-60°	244.1	15.8
60°-70°	150.2	9.7
70°-80°	58.2	3.8
80°-90°	9.3	0.6
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	479.4	31.1
0°-40°	780.2	50.6
0°-60°	1324.5	85.9
0°-90°	1542.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1542.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	621	
5°	620	59
15°	596	168
25°	550	253
35°	482	301
45°	390	300
55°	273	244
65°	151	150
75°	53	58
85°	7	9
90°	0	



TEST NUMBER: P206234

CATALOG NUMBER: LD4B20D010 EU4B10209727 4LBPSMW1

CANDELA DISTRIBUTION (FULL):

	0°
0°	621.3
2.5°	622.3
5°	619.5
7.5°	615.9
10°	611.3
12.5°	603.1
15°	595.8
17.5°	584.8
20°	572.9
22.5°	562.0
25°	550.1
27.5°	533.6
30°	517.2
32.5°	501.6
35°	481.5
37.5°	459.6
40°	439.5
42.5°	414.8
45°	390.2
47.5°	363.7
50°	335.3
52.5°	306.1
55°	273.2
57.5°	241.2
60°	210.2
62.5°	180.0
65°	150.8
67.5°	123.4
70°	97.8
72.5°	74.0
75°	53.0
77.5°	34.7
80°	21.0
82.5°	12.8
85°	7.3
87.5°	3.7
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)