

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P207665

Luminaire Tested: **LD4B15D010 EU4B10209730 4LBNH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P207665
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD4B15D010 EU4B10209730 4LBNH1
Description: PORTFOLIO 4 INCH 50 DEGREE CUTOFF RECESSED DOWNLIGHT
NARROW DISTRIBUTION WITH SEMI-SPECULAR CLEAR TRIM
WATTAGE D010TR-14.39W DE010-14.29W D5LT-14.34W DMX-14.46W DL2-15.8W
DL3-15.28W DLE-15.432W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 697.4 lumens
Efficiency: N/A
Efficacy: 48.8 lumens/watt
Spacing Criteria (0/90/45): 0.81 / 0.81 / 0.85
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P207665

CATALOG NUMBER: LD4B15D010 EU4B10209730 4LBNH1

Luminous Intensity Polar Plot






TEST NUMBER: P207665

CATALOG NUMBER: LD4B15D010 EU4B10209730 4LBNH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10		50	30	10			50	30	10			50
RCR																				
0	119	119	119	119	116	116	116	116		111	111	111			106	106	106			102
1	113	111	108	106	111	109	106	104		105	103	101			101	99	98			97
2	108	103	99	96	106	101	98	94		98	95	92			95	93	90			92
3	102	96	91	87	100	95	90	86		92	88	85			90	86	84			87
4	97	90	84	80	95	89	83	79		86	82	78			84	81	78			83
5	92	84	78	74	91	83	78	73		81	76	73			80	75	72			78
6	88	79	73	69	86	78	72	68		76	72	68			75	71	67			74
7	83	74	68	64	82	73	68	64		72	67	63			71	66	63			70
8	79	70	64	60	78	69	64	60		68	63	59			67	63	59			66
9	76	66	60	56	74	65	60	56		65	59	56			64	59	56			63
10	72	62	57	53	71	62	56	53		61	56	53			60	56	52			60

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P207665

CATALOG NUMBER: LD4B15D010 EU4B10209730 4LBNH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	79.0	11.3
10°-20°	191.6	27.5
20°-30°	222.5	31.9
30°-40°	147.3	21.1
40°-50°	41.3	5.9
50°-60°	10.4	1.5
60°-70°	3.9	0.6
70°-80°	1.4	0.2
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	493.1	70.7
0°-40°	640.4	91.8
0°-60°	692.1	99.2
0°-90°	697.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	697.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	876	
5°	853	79
15°	686	192
25°	488	222
35°	236	147
45°	48	41
55°	11	10
65°	4	4
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P207665

CATALOG NUMBER: LD4B15D010 EU4B10209730 4LBNH1

CANDELA DISTRIBUTION (FULL):

	0°
0°	875.5
2.5°	871.7
5°	852.8
7.5°	819.9
10°	779.5
12.5°	734.0
15°	686.0
17.5°	639.3
20°	587.5
22.5°	539.5
25°	487.7
27.5°	438.4
30°	375.2
32.5°	308.3
35°	236.3
37.5°	169.3
40°	115.0
42.5°	74.5
45°	48.0
47.5°	29.1
50°	19.0
52.5°	13.9
55°	11.4
57.5°	8.8
60°	6.3
62.5°	5.1
65°	3.8
67.5°	2.5
70°	2.5
72.5°	1.3
75°	1.3
77.5°	1.3
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)