

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P206841

Luminaire Tested: **LD4B15D010 EU4B10209730 4LBWGPH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P206841
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD4B15D010 EU4B10209730 4LBWGPH1
Description: PORTFOLIO 4 INCH 60 DEGREE CUTOFF RECESSED DOWNLIGHT
WIDE DISTRIBUTIONWITH GRAPHITE HAZE TRIM
WATTAGE D010TR-14.39W DE010-14.29W D5LT-14.34W DMX-14.46W DL2-15.8W
DL3-15.28W DLE-15.432W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 730.3 lumens
Efficiency: N/A
Efficacy: 51.1 lumens/watt
Spacing Criteria (0/90/45): 1.12 / 1.12 / 1.08
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P206841

CATALOG NUMBER: LD4B15D010 EU4B10209730 4LBWGPH1

Luminous Intensity Polar Plot




TEST NUMBER: P206841
CATALOG NUMBER: LD4B15D010 EU4B10209730 4LBWGPH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				0
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		0
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		100
1	113	110	107	104	110	107	105	103	103	101	99		100	98	96		92
2	106	100	96	92	104	99	95	91	95	92	89		92	90	87		83
3	100	92	87	82	98	91	86	81	88	84	80		86	82	79		76
4	94	85	78	74	92	84	78	73	81	76	72		79	75	71		69
5	88	78	72	67	86	77	71	66	75	70	66		74	69	65		63
6	83	72	65	61	81	71	65	60	70	64	60		68	63	59		57
7	78	67	60	55	76	66	60	55	65	59	55		64	58	55		53
8	73	62	56	51	72	62	55	51	61	55	50		59	54	50		48
9	69	58	51	47	68	58	51	47	57	51	47		56	50	46		45
10	65	54	48	43	64	54	48	43	53	47	43		52	47	43		41

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P206841

CATALOG NUMBER: LD4B15D010 EU4B10209730 4LBWGPH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	49.6	6.8
10°-20°	140.5	19.2
20°-30°	201.5	27.6
30°-40°	189.7	26.0
40°-50°	104.8	14.3
50°-60°	33.6	4.6
60°-70°	8.4	1.2
70°-80°	2.0	0.3
80°-90°	0.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	391.6	53.6
0°-40°	581.3	79.6
0°-60°	719.7	98.5
0°-90°	730.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	730.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	526	
5°	523	50
15°	498	140
25°	442	201
35°	308	190
45°	133	105
55°	34	34
65°	8	8
75°	1	2
85°	0	0
90°	0	



TEST NUMBER: P206841

CATALOG NUMBER: LD4B15D010 EU4B10209730 4LBWGPH1

CANDELA DISTRIBUTION (FULL):

	0°
0°	525.6
2.5°	521.8
5°	523.0
7.5°	519.2
10°	512.9
12.5°	506.6
15°	497.7
17.5°	490.1
20°	477.5
22.5°	459.7
25°	442.0
27.5°	417.9
30°	386.3
32.5°	350.8
35°	307.7
37.5°	262.2
40°	215.3
42.5°	172.2
45°	133.0
47.5°	100.0
50°	72.2
52.5°	50.7
55°	34.2
57.5°	22.8
60°	16.5
62.5°	11.4
65°	7.6
67.5°	5.1
70°	3.8
72.5°	2.5
75°	1.3
77.5°	1.3
80°	1.3
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)