

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P207151

Luminaire Tested: **LD4B20D010 EU4B10208027 4LBMH1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P207151  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LD4B20D010 EU4B10208027 4LBMH1  
Description: PORTFOLIO 4 INCH 50 DEGREE CUTOFF RECESSED DOWNLIGHT  
MEDIUM DISTRIBUTION WITH SEMI-SPECULAR CLEAR TRIM  
WATTAGE D010TR-21.86W DE010-20.46W D5LT-21.24W DMX-20.89W DL2-22.5W  
DL3-21.8 6W DLE-22.46W  
Light Source: HIGH LUMEN LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1457.1 lumens  
Efficiency: N/A  
Efficacy: 70.1 lumens/watt  
Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.93  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 20.8  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P207151

CATALOG NUMBER: LD4B20D010 EU4B10208027 4LBMH1

### Luminous Intensity Polar Plot





TEST NUMBER: P207151

CATALOG NUMBER: LD4B20D010 EU4B10208027 4LBMH1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|--|-----|-----|-----|--|-----|
| RF  | 20  |     |     |     | 20  |     |     |     | 20  |     |     |  | 20  |     |     |  | 20  |
| RC  | 80  |     |     |     | 70  |     |     |     | 50  |     |     |  | 30  |     |     |  | 10  |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  |  | 50  | 30  | 10  |  | 50  |
| RCR |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 |  | 106 | 106 | 106 |  | 102 |
| 1   | 113 | 110 | 108 | 105 | 111 | 108 | 106 | 104 | 104 | 102 | 100 |  | 100 | 99  | 97  |  | 97  |
| 2   | 107 | 102 | 98  | 94  | 105 | 100 | 96  | 93  | 97  | 94  | 91  |  | 94  | 91  | 89  |  | 91  |
| 3   | 101 | 94  | 89  | 85  | 99  | 93  | 88  | 84  | 90  | 86  | 83  |  | 88  | 84  | 82  |  | 86  |
| 4   | 96  | 88  | 82  | 77  | 94  | 86  | 81  | 77  | 84  | 80  | 76  |  | 82  | 78  | 75  |  | 80  |
| 5   | 90  | 82  | 75  | 71  | 89  | 81  | 75  | 70  | 79  | 74  | 70  |  | 77  | 73  | 69  |  | 75  |
| 6   | 86  | 76  | 70  | 65  | 84  | 75  | 69  | 65  | 74  | 68  | 64  |  | 72  | 68  | 64  |  | 71  |
| 7   | 81  | 71  | 65  | 60  | 80  | 70  | 64  | 60  | 69  | 64  | 60  |  | 68  | 63  | 59  |  | 67  |
| 8   | 77  | 67  | 60  | 56  | 75  | 66  | 60  | 56  | 65  | 59  | 56  |  | 64  | 59  | 55  |  | 63  |
| 9   | 73  | 63  | 56  | 52  | 72  | 62  | 56  | 52  | 61  | 56  | 52  |  | 60  | 55  | 52  |  | 59  |
| 10  | 69  | 59  | 53  | 49  | 68  | 59  | 53  | 49  | 58  | 52  | 49  |  | 57  | 52  | 48  |  | 56  |

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P207151

CATALOG NUMBER: LD4B20D010 EU4B10208027 4LBMH1

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 132.9  | 9.1       |
| 10°-20°   | 348.8  | 23.9      |
| 20°-30°   | 448.2  | 30.8      |
| 30°-40°   | 337.2  | 23.1      |
| 40°-50°   | 135.4  | 9.3       |
| 50°-60°   | 38.5   | 2.6       |
| 60°-70°   | 12.2   | 0.8       |
| 70°-80°   | 3.5    | 0.2       |
| 80°-90°   | 0.3    | 0.0       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-30°    | 929.9  | 63.8      |
| 0°-40°    | 1267.2 | 87.0      |
| 0°-60°    | 1441.1 | 98.9      |
| 0°-90°    | 1457.1 | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 1457.1 | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°   | Flux |
|-----|------|------|
| 0°  | 1445 |      |
| 5°  | 1418 | 133  |
| 15° | 1245 | 349  |
| 25° | 990  | 448  |
| 35° | 541  | 337  |
| 45° | 167  | 135  |
| 55° | 40   | 39   |
| 65° | 11   | 12   |
| 75° | 2    | 3    |
| 85° | 0    | 0    |
| 90° | 0    |      |



TEST NUMBER: P207151

CATALOG NUMBER: LD4B20D010 EU4B10208027 4LBMH1

**CANDELA DISTRIBUTION (FULL):**

| 0°    |        |
|-------|--------|
| 0°    | 1444.8 |
| 2.5°  | 1436.0 |
| 5°    | 1418.4 |
| 7.5°  | 1385.4 |
| 10°   | 1343.6 |
| 12.5° | 1293.1 |
| 15°   | 1244.7 |
| 17.5° | 1189.7 |
| 20°   | 1130.3 |
| 22.5° | 1066.6 |
| 25°   | 989.6  |
| 27.5° | 897.2  |
| 30°   | 789.5  |
| 32.5° | 668.5  |
| 35°   | 541.0  |
| 37.5° | 422.2  |
| 40°   | 316.7  |
| 42.5° | 233.1  |
| 45°   | 167.1  |
| 47.5° | 114.4  |
| 50°   | 79.2   |
| 52.5° | 55.0   |
| 55°   | 39.6   |
| 57.5° | 28.6   |
| 60°   | 22.0   |
| 62.5° | 15.4   |
| 65°   | 11.0   |
| 67.5° | 8.8    |
| 70°   | 6.6    |
| 72.5° | 4.4    |
| 75°   | 2.2    |
| 77.5° | 2.2    |
| 80°   | 2.2    |
| 82.5° | 0.0    |
| 85°   | 0.0    |
| 87.5° | 0.0    |
| 90°   | 0.0    |



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)