

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P208178

Luminaire Tested: **LD4B20D010 EU4B10208027 4LBMLI1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P208178
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD4B20D010 EU4B10208027 4LBMLI1
Description: PORTFOLIO 4 INCH 50 DEGREE CUTOFF RECESSED DOWNLIGHT
MEDIUM DISTRIBUTION WITH SPECULAR CLEAR TRIM
WATTAGE D010TR-21.86W DE010-20.46W D5LT-21.24W DMX-20.89W DL2-22.5W
DL3-21.8 6W DLE-22.46W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1817.5 lumens
Efficiency: N/A
Efficacy: 87.4 lumens/watt
Spacing Criteria (0/90/45): 0.7 / 0.7 / 0.76
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 20.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P208178

CATALOG NUMBER: LD4B20D010 EU4B10208027 4LBMLI1

Luminous Intensity Polar Plot





TEST NUMBER: P208178

CATALOG NUMBER: LD4B20D010 EU4B10208027 4LBMLI1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	111	109	107	111	109	107	105	105	103	102		101	100	99		98
2	109	104	100	97	107	102	99	96	99	96	94		96	94	92		94
3	104	98	93	89	102	96	92	89	94	90	87		91	88	86		89
4	99	92	87	83	97	91	86	82	89	85	81		87	83	80		85
5	94	87	81	77	93	86	81	77	84	79	76		82	78	75		81
6	90	82	76	72	89	81	76	72	80	75	71		78	74	71		77
7	86	77	72	68	85	77	71	68	75	71	67		74	70	67		73
8	82	73	68	64	81	73	67	64	72	67	64		71	66	63		70
9	79	70	64	60	78	69	64	60	68	63	60		67	63	60		67
10	75	66	61	57	74	66	61	57	65	60	57		64	60	57		64

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P208178

CATALOG NUMBER: LD4B20D010 EU4B10208027 4LBMLI1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	259.4	14.3
10°-20°	580.0	31.9
20°-30°	576.6	31.7
30°-40°	314.0	17.3
40°-50°	72.6	4.0
50°-60°	10.2	0.6
60°-70°	3.8	0.2
70°-80°	0.9	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1416.0	77.9
0°-40°	1730.1	95.2
0°-60°	1812.9	99.7
0°-90°	1817.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1817.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2865	
5°	2806	259
15°	2093	580
25°	1264	577
35°	486	314
45°	84	73
55°	11	10
65°	4	4
75°	0	1
85°	0	0
90°	0	



TEST NUMBER: P208178

CATALOG NUMBER: LD4B20D010 EU4B10208027 4LBMLI1

CANDELA DISTRIBUTION (FULL):

0°	
0°	2865.2
2.5°	2858.6
5°	2805.8
7.5°	2698.1
10°	2548.6
12.5°	2328.7
15°	2093.4
17.5°	1860.3
20°	1631.6
22.5°	1444.7
25°	1264.4
27.5°	1092.9
30°	899.4
32.5°	683.9
35°	486.0
37.5°	327.6
40°	213.3
42.5°	134.1
45°	83.6
47.5°	48.4
50°	24.2
52.5°	13.2
55°	11.0
57.5°	6.6
60°	6.6
62.5°	4.4
65°	4.4
67.5°	2.2
70°	2.2
72.5°	2.2
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)