

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P207563

Luminaire Tested: **LD4B20D010 EU4B10208027 4LBMMW1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P207563
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD4B20D010 EU4B10208027 4LBMMW1
Description: PORTFOLIO 4 INCH 50 DEGREE CUTOFF RECESSED DOWNLIGHT
MEDIUM DISTRIBUTION WITH MATTE WHITE TRIM
WATTAGE D010TR-21.86W DE010-20.46W D5LT-21.24W DMX-20.89W DL2-22.5W
DL3-21.8 6W DLE-22.46W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1516.4 lumens
Efficiency: N/A
Efficacy: 72.9 lumens/watt
Spacing Criteria (0/90/45): 0.99 / 0.99 / 0.97
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 20.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P207563

CATALOG NUMBER: LD4B20D010 EU4B10208027 4LBMMW1

Luminous Intensity Polar Plot





TEST NUMBER: P207563

CATALOG NUMBER: LD4B20D010 EU4B10208027 4LBMMW1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	108	105	102	109	106	103	100	102	99	97		98	96	94		94
2	104	98	92	88	102	96	91	87	93	89	85		89	86	83		87
3	97	89	83	77	95	87	82	77	85	80	76		82	78	74		80
4	91	81	74	69	89	80	74	69	78	72	68		76	71	67		74
5	85	75	67	62	83	74	67	62	72	66	61		70	65	61		68
6	80	69	62	56	78	68	61	56	66	60	56		65	59	55		63
7	75	64	57	52	74	63	56	51	62	56	51		60	55	51		59
8	71	59	52	47	69	59	52	47	58	51	47		56	51	47		55
9	67	55	48	44	66	55	48	44	54	48	44		53	47	43		52
10	63	52	45	41	62	51	45	41	51	45	40		50	44	40		49

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P207563

CATALOG NUMBER: LD4B20D010 EU4B10208027 4LBMMW1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	106.7	7.0
10°-20°	286.0	18.9
20°-30°	380.3	25.1
30°-40°	311.1	20.5
40°-50°	181.2	11.9
50°-60°	120.2	7.9
60°-70°	79.0	5.2
70°-80°	41.7	2.7
80°-90°	10.2	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	773.1	51.0
0°-40°	1084.2	71.5
0°-60°	1385.5	91.4
0°-90°	1516.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1516.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1151	
5°	1138	107
15°	1019	286
25°	835	380
35°	496	311
45°	228	181
55°	134	120
65°	79	79
75°	40	42
85°	9	10
90°	0	



TEST NUMBER: P207563

CATALOG NUMBER: LD4B20D010 EU4B10208027 4LBMMW1

CANDELA DISTRIBUTION (FULL):

	0°
0°	1151.1
2.5°	1148.9
5°	1138.0
7.5°	1111.6
10°	1083.0
12.5°	1056.7
15°	1019.3
17.5°	977.6
20°	942.4
22.5°	894.1
25°	834.8
27.5°	771.1
30°	689.8
32.5°	593.1
35°	496.5
37.5°	408.6
40°	331.7
42.5°	272.4
45°	228.5
47.5°	193.3
50°	169.2
52.5°	149.4
55°	134.0
57.5°	118.6
60°	103.3
62.5°	92.3
65°	79.1
67.5°	68.1
70°	57.1
72.5°	48.3
75°	39.5
77.5°	30.8
80°	22.0
82.5°	15.4
85°	8.8
87.5°	2.2
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)