

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P207975

Luminaire Tested: **LD4B20D010 EU4B10208027 4LBNMW1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P207975
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD4B20D010 EU4B10208027 4LBNMW1
Description: PORTFOLIO 4 INCH 50 DEGREE CUTOFF RECESSED DOWNLIGHT
NARROW DISTRIBUTION WITH MATTE WHITE TRIM
WATTAGE D010TR-21.86W DE010-20.46W D5LT-21.24W DMX-20.89W DL2-22.5W
DL3-21.8 6W DLE-22.46W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1382.3 lumens
Efficiency: N/A
Efficacy: 66.5 lumens/watt
Spacing Criteria (0/90/45): 0.96 / 0.96 / 0.95
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 20.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P207975

CATALOG NUMBER: LD4B20D010 EU4B10208027 4LBNMW1

Luminous Intensity Polar Plot





TEST NUMBER: P207975

CATALOG NUMBER: LD4B20D010 EU4B10208027 4LBNMW1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10		50	30	10			50	30	10			50
RCR																				
0	119	119	119	119	116	116	116	116		111	111	111			106	106	106			102
1	112	109	105	103	109	106	104	101		102	100	98			98	97	95			95
2	105	99	94	90	103	97	93	89		94	90	87			91	88	85			88
3	98	90	84	80	96	89	83	79		86	82	78			84	80	76			81
4	92	83	76	71	90	82	76	71		80	74	70			78	73	69			76
5	87	77	70	65	85	76	69	64		74	68	64			72	67	63			70
6	82	71	64	59	80	70	64	59		69	63	58			67	62	58			66
7	77	66	59	54	75	65	59	54		64	58	54			63	57	53			62
8	73	62	55	50	71	61	55	50		60	54	50			59	53	49			58
9	69	58	51	46	68	57	51	46		56	50	46			55	50	46			54
10	65	54	48	43	64	54	47	43		53	47	43			52	47	43			51

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P207975

CATALOG NUMBER: LD4B20D010 EU4B10208027 4LBNMW1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	108.5	7.8
10°-20°	283.8	20.5
20°-30°	373.6	27.0
30°-40°	290.8	21.0
40°-50°	141.2	10.2
50°-60°	89.2	6.5
60°-70°	57.6	4.2
70°-80°	30.1	2.2
80°-90°	7.5	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	765.9	55.4
0°-40°	1056.7	76.4
0°-60°	1287.2	93.1
0°-90°	1382.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1382.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1179	
5°	1157	108
15°	1012	284
25°	824	374
35°	466	291
45°	176	141
55°	99	89
65°	57	58
75°	28	30
85°	7	7
90°	0	



TEST NUMBER: P207975

CATALOG NUMBER: LD4B20D010 EU4B10208027 4LBNMW1

CANDELA DISTRIBUTION (FULL):

0°	
0°	1179.2
2.5°	1172.7
5°	1157.3
7.5°	1130.9
10°	1095.8
12.5°	1056.3
15°	1012.4
17.5°	966.2
20°	917.9
22.5°	871.8
25°	823.5
27.5°	762.0
30°	678.6
32.5°	579.7
35°	465.5
37.5°	360.1
40°	278.9
42.5°	217.4
45°	175.7
47.5°	142.7
50°	125.2
52.5°	112.0
55°	98.8
57.5°	87.8
60°	76.9
62.5°	65.9
65°	57.1
67.5°	50.5
70°	41.7
72.5°	35.1
75°	28.5
77.5°	22.0
80°	15.4
82.5°	11.0
85°	6.6
87.5°	2.2
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)