

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P207571

Luminaire Tested: **LD4B20D010 EU4B10209035 4LBMMW1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P207571
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD4B20D010 EU4B10209035 4LBMMW1
Description: PORTFOLIO 4 INCH 50 DEGREE CUTOFF RECESSED DOWNLIGHT
MEDIUM DISTRIBUTION WITH MATTE WHITE TRIM
WATTAGE D010TR-21.86W DE010-20.46W D5LT-21.24W DMX-20.89W DL2-22.5W
DL3-21.8 6W DLE-22.46W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1373.1 lumens
Efficiency: N/A
Efficacy: 66.0 lumens/watt
Spacing Criteria (0/90/45): 0.99 / 0.99 / 0.97
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 20.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P207571

CATALOG NUMBER: LD4B20D010 EU4B10209035 4LBMMW1

Luminous Intensity Polar Plot






TEST NUMBER: P207571

CATALOG NUMBER: LD4B20D010 EU4B10209035 4LBMMW1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	108	105	102	109	106	103	100	102	99	97		98	96	94		94
2	104	98	92	88	102	96	91	87	93	89	85		89	86	83		87
3	97	89	83	77	95	87	82	77	85	80	76		82	78	74		80
4	91	81	74	69	89	80	74	69	78	72	68		76	71	67		74
5	85	75	67	62	83	74	67	62	72	66	61		70	65	61		68
6	80	69	62	56	78	68	61	56	66	60	56		65	59	55		63
7	75	64	57	52	74	63	56	51	62	56	51		60	55	51		59
8	71	59	52	47	69	59	52	47	58	51	47		56	51	47		55
9	67	55	48	44	66	55	48	44	54	48	44		53	47	43		52
10	63	52	45	41	62	51	45	41	51	45	40		50	44	40		49

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P207571

CATALOG NUMBER: LD4B20D010 EU4B10209035 4LBMMW1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	96.6	7.0
10°-20°	259.0	18.9
20°-30°	344.4	25.1
30°-40°	281.7	20.5
40°-50°	164.1	12.0
50°-60°	108.8	7.9
60°-70°	71.5	5.2
70°-80°	37.7	2.7
80°-90°	9.2	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	700.0	51.0
0°-40°	981.7	71.5
0°-60°	1254.6	91.4
0°-90°	1373.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1373.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1042	
5°	1030	97
15°	923	259
25°	756	344
35°	450	282
45°	207	164
55°	121	109
65°	72	72
75°	36	38
85°	8	9
90°	0	



TEST NUMBER: P207571

CATALOG NUMBER: LD4B20D010 EU4B10209035 4LBMMW1

CANDELA DISTRIBUTION (FULL):

	0°
0°	1042.4
2.5°	1040.4
5°	1030.4
7.5°	1006.6
10°	980.7
12.5°	956.8
15°	923.0
17.5°	885.2
20°	853.4
22.5°	809.6
25°	755.9
27.5°	698.2
30°	624.6
32.5°	537.1
35°	449.6
37.5°	370.0
40°	300.4
42.5°	246.7
45°	206.9
47.5°	175.1
50°	153.2
52.5°	135.3
55°	121.3
57.5°	107.4
60°	93.5
62.5°	83.5
65°	71.6
67.5°	61.7
70°	51.7
72.5°	43.8
75°	35.8
77.5°	27.8
80°	19.9
82.5°	13.9
85°	8.0
87.5°	2.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)