

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P208077

Luminaire Tested: **LD4B20D010 EU4B10208027 4LBWLI1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P208077
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD4B20D010 EU4B10208027 4LBWLI1
Description: PORTFOLIO 4 INCH 60 DEGREE CUTOFF RECESSED DOWNLIGHT
WIDE DISTRIBUTION WITH SPECULAR CLEAR TRIM
WATTAGE D010TR-21.86W DE010-20.46W D5LT-21.24W DMX-20.89W DL2-22.5W
DL3-21.8 6W DLE-22.46W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1918.6 lumens
Efficiency: N/A
Efficacy: 92.2 lumens/watt
Spacing Criteria (0/90/45): 1.29 / 1.29 / 1.18
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 20.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P208077

CATALOG NUMBER: LD4B20D010 EU4B10208027 4LBWLI1

Luminous Intensity Polar Plot





TEST NUMBER: P208077

CATALOG NUMBER: LD4B20D010 EU4B10208027 4LBWLI1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	107	105	110	108	105	103	104	102	100		100	98	97		96
2	106	101	97	93	104	99	95	92	96	93	90		93	90	88		90
3	100	93	87	83	98	92	86	82	89	85	81		86	83	80		84
4	94	86	79	75	92	84	79	74	82	77	73		80	76	72		78
5	88	79	72	68	87	78	72	67	76	71	67		74	70	66		73
6	83	73	66	62	82	72	66	61	71	65	61		69	64	60		68
7	78	68	61	56	77	67	61	56	66	60	56		64	59	55		63
8	74	63	56	52	72	62	56	51	61	55	51		60	55	51		59
9	69	59	52	48	68	58	52	47	57	51	47		56	51	47		55
10	66	55	48	44	65	54	48	44	53	48	44		53	47	44		52

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P208077

CATALOG NUMBER: LD4B20D010 EU4B10208027 4LBWLI1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	115.0	6.0
10°-20°	362.8	18.9
20°-30°	565.9	29.5
30°-40°	550.7	28.7
40°-50°	275.0	14.3
50°-60°	42.6	2.2
60°-70°	5.2	0.3
70°-80°	1.4	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1043.7	54.4
0°-40°	1594.4	83.1
0°-60°	1912.0	99.7
0°-90°	1918.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1918.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1176	
5°	1191	115
15°	1281	363
25°	1244	566
35°	894	551
45°	345	275
55°	35	43
65°	4	5
75°	2	1
85°	0	0
90°	0	



TEST NUMBER: P208077

CATALOG NUMBER: LD4B20D010 EU4B10208027 4LBWLI1

CANDELA DISTRIBUTION (FULL):

0°	
0°	1175.5
2.5°	1179.9
5°	1190.9
7.5°	1208.5
10°	1230.5
12.5°	1259.0
15°	1281.0
17.5°	1298.6
20°	1300.8
22.5°	1285.4
25°	1243.7
27.5°	1182.1
30°	1105.2
32.5°	1008.6
35°	894.3
37.5°	769.0
40°	637.2
42.5°	496.6
45°	345.0
47.5°	221.9
50°	134.0
52.5°	72.5
55°	35.2
57.5°	15.4
60°	8.8
62.5°	6.6
65°	4.4
67.5°	4.4
70°	2.2
72.5°	2.2
75°	2.2
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)