

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P208389

Luminaire Tested: **LD4B20D010 EU4B10209035 4LBSLI1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P208389
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD4B20D010 EU4B10209035 4LBSLI1
Description: PORTFOLIO 4 INCH SHALLOW RECESSED DOWNLIGHT
SHALLOW DISTRIBUTION WITH SPECULAR CLEAR TRIM
WATTAGE D010TR-21.86W DE010-20.46W D5LT-21.24W DMX-20.89W DL2-22.5W
DL3-21.8 6W DLE-22.46W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1797.0 lumens
Efficiency: N/A
Efficacy: 86.4 lumens/watt
Spacing Criteria (0/90/45): 0.91 / 0.91 / 1
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 20.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P208389

CATALOG NUMBER: LD4B20D010 EU4B10209035 4LBSLI1

Luminous Intensity Polar Plot






TEST NUMBER: P208389

CATALOG NUMBER: LD4B20D010 EU4B10209035 4LBSLI1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10		50	30	10			50	30	10			50
RCR																				
0	119	119	119	119	116	116	116	116		111	111	111			106	106	106			102
1	112	108	105	102	109	106	103	101		102	100	98			98	96	95			95
2	104	98	93	88	102	96	91	87		93	89	85			90	86	84			87
3	97	89	82	77	95	87	81	77		84	79	75			82	78	74			79
4	90	81	73	68	88	79	73	68		77	71	67			75	70	66			73
5	84	73	66	61	82	72	65	60		70	64	60			69	63	59			67
6	79	67	60	54	77	66	59	54		65	58	54			63	58	53			62
7	74	62	54	49	72	61	54	49		60	53	49			58	53	48			57
8	69	57	50	45	68	57	50	45		55	49	45			54	49	44			53
9	65	53	46	41	64	53	46	41		52	45	41			51	45	41			50
10	61	50	43	38	60	49	42	38		48	42	38			47	42	38			46

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P208389

CATALOG NUMBER: LD4B20D010 EU4B10209035 4LBSLI1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	116.3	6.5
10°-20°	296.7	16.5
20°-30°	384.5	21.4
30°-40°	376.7	21.0
40°-50°	319.3	17.8
50°-60°	209.3	11.6
60°-70°	84.2	4.7
70°-80°	9.6	0.5
80°-90°	0.3	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	797.6	44.4
0°-40°	1174.3	65.3
0°-60°	1703.0	94.8
0°-90°	1797.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1797.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1283	
5°	1249	116
15°	1058	297
25°	840	385
35°	599	377
45°	416	319
55°	233	209
65°	82	84
75°	4	10
85°	0	0
90°	0	



TEST NUMBER: P208389

CATALOG NUMBER: LD4B20D010 EU4B10209035 4LBSLI1

CANDELA DISTRIBUTION (FULL):

0°	
0°	1283.1
2.5°	1273.1
5°	1249.3
7.5°	1209.5
10°	1159.8
12.5°	1106.0
15°	1058.3
17.5°	1006.6
20°	954.9
22.5°	899.2
25°	839.5
27.5°	777.8
30°	714.2
32.5°	654.5
35°	598.8
37.5°	553.0
40°	503.3
42.5°	459.5
45°	415.8
47.5°	370.0
50°	324.3
52.5°	278.5
55°	232.7
57.5°	191.0
60°	151.2
62.5°	115.4
65°	81.6
67.5°	53.7
70°	31.8
72.5°	13.9
75°	4.0
77.5°	2.0
80°	2.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)