

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P206539

Luminaire Tested: **LD4B20D010 EU4B10209027 4LBCSMMS1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P206539
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD4B20D010 EU4B10209027 4LBSCMMS1
Description: PORTFOLIO 4 INCH SHALLOW RECESSED DOWNLIGHT
SHALLOW DISTRIBUTION WITH CAST MATTE BLACK TRIM
WATTAGE D010TR-21.86W DE010-20.46W D5LT-21.24W DMX-20.89W DL2-22.5W
DL3-21.8 6W DLE-22.46W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1466.1 lumens
Efficiency: N/A
Efficacy: 70.5 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.16 / 1.27
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 20.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P206539

CATALOG NUMBER: LD4B20D010 EU4B10209027 4LBCSMMS1

Luminous Intensity Polar Plot






TEST NUMBER: P206539

CATALOG NUMBER: LD4B20D010 EU4B10209027 4LBCSMMS1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	111	107	103	100	108	105	101	98	100	98	95	97	94	92	93	91	90	88		
2	102	95	89	84	99	93	88	83	90	85	81	86	83	79	83	80	78	76		
3	94	85	77	72	92	83	76	71	80	74	70	77	73	69	75	71	67	65		
4	87	76	68	62	84	74	67	61	72	66	61	70	64	60	68	63	59	57		
5	80	68	60	54	78	67	59	54	65	58	53	63	57	53	61	56	52	50		
6	74	62	54	48	72	61	53	47	59	52	47	58	51	47	56	51	46	44		
7	69	56	48	42	67	56	48	42	54	47	42	53	46	42	51	46	41	40		
8	64	52	44	38	63	51	43	38	50	43	38	48	42	38	47	42	37	36		
9	60	48	40	35	59	47	40	34	46	39	34	45	39	34	44	38	34	32		
10	57	44	36	31	55	43	36	31	43	36	31	42	35	31	41	35	31	29		

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P206539

CATALOG NUMBER: LD4B20D010 EU4B10209027 4LBCSMMS1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	63.5	4.3
10°-20°	178.0	12.1
20°-30°	260.1	17.7
30°-40°	297.4	20.3
40°-50°	285.9	19.5
50°-60°	220.7	15.1
60°-70°	123.2	8.4
70°-80°	35.9	2.4
80°-90°	1.5	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	501.5	34.2
0°-40°	799.0	54.5
0°-60°	1305.5	89.0
0°-90°	1466.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1466.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	673	
5°	668	63
15°	632	178
25°	565	260
35°	476	297
45°	373	286
55°	248	221
65°	123	123
75°	31	36
85°	1	2
90°	0	



TEST NUMBER: P206539

CATALOG NUMBER: LD4B20D010 EU4B10209027 4LBCSMMS1

CANDELA DISTRIBUTION (FULL):

	0°
0°	673.3
2.5°	673.3
5°	667.6
7.5°	664.8
10°	655.3
12.5°	643.9
15°	631.6
17.5°	619.2
20°	601.2
22.5°	587.0
25°	565.2
27.5°	543.4
30°	521.6
32.5°	499.8
35°	476.0
37.5°	452.3
40°	424.8
42.5°	400.2
45°	372.7
47.5°	341.4
50°	312.0
52.5°	279.7
55°	247.5
57.5°	214.3
60°	183.0
62.5°	151.7
65°	123.3
67.5°	96.7
70°	72.1
72.5°	50.3
75°	31.3
77.5°	16.1
80°	5.7
82.5°	1.9
85°	0.9
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)