

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P206021

Luminaire Tested: **LD4B20D010 EU4B10209027 4LBSB1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P206021
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD4B20D010 EU4B10209027 4LBSB1
Description: PORTFOLIO 4 INCH SHALLOW RECESSED DOWNLIGHT
SHALLOW DISTRIBUTION WITH SPECULAR BLACK TRIM
WATTAGE D010TR-21.86W DE010-20.46W D5LT-21.24W DMX-20.89W DL2-22.5W
DL3-21.8 6W DLE-22.46W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1435.4 lumens
Efficiency: N/A
Efficacy: 69.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.2 / 1.3
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 20.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P206021

CATALOG NUMBER: LD4B20D010 EU4B10209027 4LBSB1

Luminous Intensity Polar Plot





TEST NUMBER: P206021

CATALOG NUMBER: LD4B20D010 EU4B10209027 4LBSB1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	111	107	103	100	108	105	101	98	100	98	95	97	94	93	93	91	90	88		
2	102	95	89	84	100	93	88	83	90	85	81	86	83	79	84	80	78	76		
3	94	84	77	72	91	83	76	71	80	74	70	77	73	69	75	71	67	65		
4	86	76	68	62	84	74	67	61	72	65	60	70	64	60	68	63	59	57		
5	80	68	60	54	78	67	59	53	65	58	53	63	57	52	61	56	52	50		
6	74	62	53	47	72	61	53	47	59	52	47	57	51	46	56	50	46	44		
7	69	56	48	42	67	55	48	42	54	47	42	52	46	41	51	45	41	39		
8	64	51	43	38	63	51	43	38	49	42	37	48	42	37	47	41	37	35		
9	60	47	39	34	59	47	39	34	46	39	34	45	38	34	44	38	34	32		
10	56	44	36	31	55	43	36	31	42	36	31	41	35	31	40	35	31	29		

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P206021

CATALOG NUMBER: LD4B20D010 EU4B10209027 4LBSB1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	59.8	4.2
10°-20°	169.6	11.8
20°-30°	252.3	17.6
30°-40°	293.5	20.4
40°-50°	286.1	19.9
50°-60°	220.1	15.3
60°-70°	121.6	8.5
70°-80°	32.2	2.2
80°-90°	0.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	481.6	33.6
0°-40°	775.2	54.0
0°-60°	1281.4	89.3
0°-90°	1435.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1435.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	633	
5°	630	60
15°	600	170
25°	548	252
35°	471	294
45°	371	286
55°	246	220
65°	122	122
75°	27	32
85°	0	0
90°	0	



TEST NUMBER: P206021

CATALOG NUMBER: LD4B20D010 EU4B10209027 4LBSB1

CANDELA DISTRIBUTION (FULL):

	0°
0°	633.3
2.5°	633.3
5°	629.6
7.5°	624.2
10°	620.5
12.5°	609.6
15°	600.5
17.5°	591.4
20°	578.7
22.5°	565.9
25°	547.7
27.5°	529.5
30°	511.3
32.5°	491.3
35°	471.3
37.5°	445.8
40°	424.0
42.5°	400.3
45°	371.2
47.5°	343.9
50°	313.0
52.5°	280.2
55°	245.7
57.5°	212.9
60°	182.0
62.5°	151.0
65°	121.9
67.5°	94.6
70°	69.1
72.5°	47.3
75°	27.3
77.5°	12.7
80°	1.8
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)