

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P208181

Luminaire Tested: **LD4B20D010 EU4B10208040 4LBMLI1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P208181
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD4B20D010 EU4B10208040 4LBMLI1
Description: PORTFOLIO 4 INCH 50 DEGREE CUTOFF RECESSED DOWNLIGHT
MEDIUM DISTRIBUTION WITH SPECULAR CLEAR TRIM
WATTAGE D010TR-21.86W DE010-20.46W D5LT-21.24W DMX-20.89W DL2-22.5W
DL3-21.8 6W DLE-22.46W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1967.6 lumens
Efficiency: N/A
Efficacy: 94.6 lumens/watt
Spacing Criteria (0/90/45): 0.7 / 0.7 / 0.76
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 20.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P208181

CATALOG NUMBER: LD4B20D010 EU4B10208040 4LBMLI1

Luminous Intensity Polar Plot





TEST NUMBER: P208181

CATALOG NUMBER: LD4B20D010 EU4B10208040 4LBMLI1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10		50	30	10			50	30	10			50
RCR																				
0	119	119	119	119	116	116	116	116		111	111	111			106	106	106			102
1	114	111	109	107	111	109	107	105		105	103	102			101	100	99			98
2	109	104	100	97	107	102	99	96		99	96	94			96	94	92			94
3	104	98	93	89	102	96	92	89		94	90	87			91	88	86			89
4	99	92	87	83	97	91	86	82		89	85	81			87	83	80			85
5	94	87	81	77	93	86	81	77		84	79	76			82	78	75			81
6	90	82	76	72	89	81	76	72		80	75	71			78	74	71			77
7	86	77	72	68	85	77	71	68		75	71	67			74	70	67			73
8	82	73	68	64	81	73	67	64		72	67	64			71	66	63			70
9	79	70	64	60	78	69	64	60		68	63	60			67	63	60			67
10	75	66	61	57	74	66	61	57		65	60	57			64	60	57			64

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P208181

CATALOG NUMBER: LD4B20D010 EU4B10208040 4LBMLI1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	280.8	14.3
10°-20°	627.9	31.9
20°-30°	624.2	31.7
30°-40°	339.9	17.3
40°-50°	78.6	4.0
50°-60°	11.1	0.6
60°-70°	4.1	0.2
70°-80°	0.9	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1532.9	77.9
0°-40°	1872.9	95.2
0°-60°	1962.5	99.7
0°-90°	1967.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1967.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3102	
5°	3038	281
15°	2266	628
25°	1369	624
35°	526	340
45°	90	79
55°	12	11
65°	5	4
75°	0	1
85°	0	0
90°	0	



TEST NUMBER: P208181

CATALOG NUMBER: LD4B20D010 EU4B10208040 4LBMLI1

CANDELA DISTRIBUTION (FULL):

	0°
0°	3101.8
2.5°	3094.7
5°	3037.5
7.5°	2920.9
10°	2759.0
12.5°	2521.0
15°	2266.2
17.5°	2013.9
20°	1766.3
22.5°	1564.0
25°	1368.8
27.5°	1183.1
30°	973.6
32.5°	740.3
35°	526.1
37.5°	354.7
40°	230.9
42.5°	145.2
45°	90.5
47.5°	52.4
50°	26.2
52.5°	14.3
55°	11.9
57.5°	7.1
60°	7.1
62.5°	4.8
65°	4.8
67.5°	2.4
70°	2.4
72.5°	2.4
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)