

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P206125

Luminaire Tested: **LD4B20D010 EU4B10209027 4LBSMW1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P206125
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD4B20D010 EU4B10209027 4LBSMW1
Description: PORTFOLIO 4 INCH SHALLOW RECESSED DOWNLIGHT
SHALLOW DISTRIBUTION WITH MATTE WHITE TRIM
WATTAGE D010TR-21.86W DE010-20.46W D5LT-21.24W DMX-20.89W DL2-22.5W
DL3-21.8 6W DLE-22.46W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1703.1 lumens
Efficiency: N/A
Efficacy: 81.9 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.24 / 1.34
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 20.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P206125

CATALOG NUMBER: LD4B20D010 EU4B10209027 4LBSMW1

Luminous Intensity Polar Plot






TEST NUMBER: P206125

CATALOG NUMBER: LD4B20D010 EU4B10209027 4LBSMW1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20				20
RC	80				70					50					30				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	0
RCR																			
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	
1	110	106	102	99	107	104	100	97	99	97	94	96	93	91	92	90	88	86	
2	101	93	87	82	98	92	86	81	88	83	79	85	81	77	82	79	76	74	
3	93	83	75	69	90	81	74	69	78	72	67	76	70	66	73	69	65	63	
4	85	74	66	59	83	72	65	59	70	63	58	68	62	57	66	61	56	54	
5	78	66	58	51	76	65	57	51	63	56	51	61	55	50	59	54	49	47	
6	73	60	51	45	71	59	51	45	57	50	44	55	49	44	54	48	44	42	
7	67	54	46	40	66	54	46	40	52	45	40	51	44	39	49	43	39	37	
8	63	50	41	36	61	49	41	36	48	41	35	46	40	35	45	39	35	33	
9	59	46	38	32	57	45	37	32	44	37	32	43	36	32	42	36	32	30	
10	55	42	34	29	54	42	34	29	41	34	29	40	33	29	39	33	29	27	

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P206125

CATALOG NUMBER: LD4B20D010 EU4B10209027 4LBSMW1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	65.0	3.8
10°-20°	185.3	10.9
20°-30°	279.1	16.4
30°-40°	332.1	19.5
40°-50°	331.5	19.5
50°-60°	269.6	15.8
60°-70°	165.9	9.7
70°-80°	64.2	3.8
80°-90°	10.3	0.6
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	529.5	31.1
0°-40°	861.6	50.6
0°-60°	1462.8	85.9
0°-90°	1703.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1703.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	686	
5°	684	65
15°	658	185
25°	608	279
35°	532	332
45°	431	332
55°	302	270
65°	166	166
75°	58	64
85°	8	10
90°	0	



TEST NUMBER: P206125

CATALOG NUMBER: LD4B20D010 EU4B10209027 4LBSMW1

CANDELA DISTRIBUTION (FULL):

	0°
0°	686.2
2.5°	687.2
5°	684.2
7.5°	680.2
10°	675.1
12.5°	666.0
15°	658.0
17.5°	645.9
20°	632.7
22.5°	620.6
25°	607.5
27.5°	589.4
30°	571.2
32.5°	554.0
35°	531.8
37.5°	507.6
40°	485.4
42.5°	458.2
45°	430.9
47.5°	401.6
50°	370.4
52.5°	338.1
55°	301.7
57.5°	266.4
60°	232.1
62.5°	198.8
65°	166.5
67.5°	136.2
70°	108.0
72.5°	81.7
75°	58.5
77.5°	38.3
80°	23.2
82.5°	14.1
85°	8.1
87.5°	4.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)