

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P206948

Luminaire Tested: **LD4B20D010 EU4B10208040 4LBWB1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P206948
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD4B20D010 EU4B10208040 4LBWB1
Description: PORTFOLIO 4 INCH 60 DEGREE CUTOFF RECESSED DOWNLIGHT
WIDE DISTRIBUTION WITH SPECULAR BLACK TRIM
WATTAGE D010TR-21.86W DE010-20.46W D5LT-21.24W DMX-20.89W DL2-22.5W
DL3-21.8 6W DLE-22.46W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1025.4 lumens
Efficiency: N/A
Efficacy: 49.3 lumens/watt
Spacing Criteria (0/90/45): 1.08 / 1.08 / 1.03
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 20.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P206948

CATALOG NUMBER: LD4B20D010 EU4B10208040 4LBWB1

Luminous Intensity Polar Plot





TEST NUMBER: P206948

CATALOG NUMBER: LD4B20D010 EU4B10208040 4LBWB1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	113	110	108	105		111	108	106	104		104	102	100		100	99	97		97	96	95
2	107	102	98	94		105	100	96	93		97	94	91		94	91	89		91	89	87
3	101	94	89	85		99	93	88	84		90	86	83		88	84	82		86	83	80
4	96	88	82	77		94	86	81	77		84	79	76		82	78	75		80	77	74
5	90	81	75	70		89	80	74	70		79	73	69		77	72	69		75	71	68
6	85	76	69	65		84	75	69	64		73	68	64		72	67	64		70	66	63
7	80	71	64	60		79	70	64	59		69	63	59		67	62	59		66	62	58
8	76	66	60	55		75	65	59	55		64	59	55		63	58	54		62	58	54
9	72	62	55	51		71	61	55	51		60	55	51		59	54	51		58	54	50
10	68	58	52	48		67	58	52	48		57	51	47		56	51	47		55	50	47

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P206948

CATALOG NUMBER: LD4B20D010 EU4B10208040 4LBWB1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	80.8	7.9
10°-20°	229.0	22.3
20°-30°	316.5	30.9
30°-40°	271.0	26.4
40°-50°	115.2	11.2
50°-60°	12.9	1.3
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	626.3	61.1
0°-40°	897.3	87.5
0°-60°	1025.4	100.0
0°-90°	1025.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1025.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	856	
5°	851	81
15°	813	229
25°	694	317
35°	440	271
45°	145	115
55°	7	13
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P206948

CATALOG NUMBER: LD4B20D010 EU4B10208040 4LBWB1

CANDELA DISTRIBUTION (FULL):

0°	
0°	856.0
2.5°	853.6
5°	851.2
7.5°	846.4
10°	836.9
12.5°	832.2
15°	813.2
17.5°	796.5
20°	770.4
22.5°	739.5
25°	694.3
27.5°	644.3
30°	587.3
32.5°	518.3
35°	439.9
37.5°	359.0
40°	278.2
42.5°	206.9
45°	145.0
47.5°	90.4
50°	52.3
52.5°	26.2
55°	7.1
57.5°	0.0
60°	0.0
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)