

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P206441

Luminaire Tested: **LD4B20D010 EU4B10209727 4LBCSMB1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P206441
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD4B20D010 EU4B10209727 4LBSCMB1
Description: PORTFOLIO 4 INCH SHALLOW RECESSED DOWNLIGHT
SHALLOW DISTRIBUTION WITH CAST MATTE METALLIC SILVER TRIM
WATTAGE D010TR-21.86W DE010-20.46W D5LT-21.24W DMX-20.89W DL2-22.5W
DL3-21.8 6W DLE-22.46W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1413.3 lumens
Efficiency: N/A
Efficacy: 67.9 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.23 / 1.33
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 20.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P206441

CATALOG NUMBER: LD4B20D010 EU4B10209727 4LBCSMB1

Luminous Intensity Polar Plot





TEST NUMBER: P206441

CATALOG NUMBER: LD4B20D010 EU4B10209727 4LBCSMB1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																				
0	119	119	119	119	116	116	116	116		111	111	111		106	106	106		102	102	102
1	111	107	103	100	108	104	101	98		100	98	95		96	94	92		93	91	90
2	102	95	89	84	99	93	87	83		89	85	81		86	82	79		83	80	77
3	93	84	77	71	91	83	76	70		80	74	69		77	72	68		74	70	67
4	86	75	67	61	84	74	66	61		71	65	60		69	63	59		67	62	58
5	79	67	59	53	77	66	59	53		64	57	52		62	56	52		61	55	51
6	74	61	53	47	72	60	52	46		58	51	46		57	50	46		55	50	45
7	68	55	47	41	67	55	47	41		53	46	41		52	45	41		50	45	40
8	64	51	43	37	62	50	42	37		49	42	37		48	41	37		46	41	36
9	60	47	39	33	58	46	39	33		45	38	33		44	38	33		43	37	33
10	56	43	35	30	55	43	35	30		42	35	30		41	34	30		40	34	30

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P206441

CATALOG NUMBER: LD4B20D010 EU4B10209727 4LBCSMB1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	56.4	4.0
10°-20°	160.8	11.4
20°-30°	241.7	17.1
30°-40°	286.8	20.3
40°-50°	283.8	20.1
50°-60°	223.0	15.8
60°-70°	125.0	8.8
70°-80°	35.1	2.5
80°-90°	0.6	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	459.0	32.5
0°-40°	745.8	52.8
0°-60°	1252.6	88.6
0°-90°	1413.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1413.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	597	
5°	596	56
15°	570	161
25°	525	242
35°	460	287
45°	370	284
55°	251	223
65°	125	125
75°	30	35
85°	0	1
90°	0	



TEST NUMBER: P206441

CATALOG NUMBER: LD4B20D010 EU4B10209727 4LBCSMB1

CANDELA DISTRIBUTION (FULL):

0°	
0°	596.8
2.5°	594.7
5°	595.8
7.5°	590.7
10°	584.6
12.5°	577.5
15°	570.4
17.5°	561.3
20°	549.2
22.5°	537.0
25°	524.8
27.5°	511.7
30°	494.4
32.5°	477.2
35°	460.0
37.5°	439.7
40°	416.4
42.5°	394.1
45°	369.8
47.5°	342.5
50°	314.1
52.5°	281.7
55°	251.3
57.5°	216.8
60°	184.4
62.5°	155.0
65°	124.6
67.5°	98.3
70°	72.9
72.5°	49.6
75°	30.4
77.5°	15.2
80°	4.1
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)