

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P206639

Luminaire Tested: **LD4B20D010 EU4B10208040 4LBWH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P206639
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD4B20D010 EU4B10208040 4LBWH1
Description: PORTFOLIO 4 INCH 60 DEGREE CUTOFF RECESSED DOWNLIGHT
WIDE DISTRIBUTION WITH SEMI-SPECULAR CLEAR TRIM
WATTAGE D010TR-21.86W DE010-20.46W D5LT-21.24W DMX-20.89W DL2-22.5W
DL3-21.8 6W DLE-22.46W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1753.5 lumens
Efficiency: N/A
Efficacy: 84.3 lumens/watt
Spacing Criteria (0/90/45): 1.18 / 1.18 / 1.13
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 20.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P206639

CATALOG NUMBER: LD4B20D010 EU4B10208040 4LBWH1

Luminous Intensity Polar Plot





TEST NUMBER: P206639

CATALOG NUMBER: LD4B20D010 EU4B10208040 4LBWH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10		50	30	10			50	30	10			50
RCR																				
0	119	119	119	119	116	116	116	116		111	111	111			106	106	106			102
1	112	109	106	104	110	107	104	102		103	101	99			99	97	96			96
2	105	100	95	91	103	98	93	90		95	91	88			91	88	86			89
3	99	91	85	80	97	90	84	80		87	82	78			84	80	77			82
4	92	83	77	72	90	82	76	71		80	75	70			78	73	70			76
5	87	77	70	65	85	76	69	64		74	68	64			72	67	63			70
6	81	71	64	58	80	70	63	58		68	62	58			67	61	57			65
7	76	65	58	53	75	65	58	53		63	57	53			62	56	52			61
8	72	60	53	49	70	60	53	49		59	53	48			58	52	48			57
9	68	56	49	45	66	56	49	45		55	49	44			54	48	44			53
10	64	52	46	41	63	52	46	41		51	45	41			50	45	41			49

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P206639

CATALOG NUMBER: LD4B20D010 EU4B10208040 4LBWH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	107.6	6.1
10°-20°	310.1	17.7
20°-30°	457.6	26.1
30°-40°	451.6	25.8
40°-50°	276.4	15.8
50°-60°	106.0	6.0
60°-70°	33.1	1.9
70°-80°	9.7	0.6
80°-90°	1.3	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	875.4	49.9
0°-40°	1327.0	75.7
0°-60°	1709.3	97.5
0°-90°	1753.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1753.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1130	
5°	1130	108
15°	1099	310
25°	1002	458
35°	733	452
45°	354	276
55°	112	106
65°	31	33
75°	10	10
85°	0	1
90°	0	



TEST NUMBER: P206639

CATALOG NUMBER: LD4B20D010 EU4B10208040 4LBWH1

CANDELA DISTRIBUTION (FULL):

	0°
0°	1130.2
2.5°	1132.6
5°	1130.2
7.5°	1127.8
10°	1120.7
12.5°	1111.1
15°	1099.2
17.5°	1085.0
20°	1063.6
22.5°	1039.8
25°	1001.7
27.5°	954.1
30°	894.6
32.5°	820.9
35°	732.8
37.5°	635.3
40°	535.3
42.5°	442.6
45°	354.5
47.5°	276.0
50°	209.4
52.5°	154.7
55°	111.8
57.5°	78.5
60°	57.1
62.5°	42.8
65°	30.9
67.5°	23.8
70°	16.7
72.5°	11.9
75°	9.5
77.5°	4.8
80°	4.8
82.5°	2.4
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)