

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P207160

Luminaire Tested: **LD4B20D010 EU4B10209040 4LBMH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P207160
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD4B20D010 EU4B10209040 4LBMH1
Description: PORTFOLIO 4 INCH 50 DEGREE CUTOFF RECESSED DOWNLIGHT
MEDIUM DISTRIBUTION WITH SEMI-SPECULAR CLEAR TRIM
WATTAGE D010TR-21.86W DE010-20.46W D5LT-21.24W DMX-20.89W DL2-22.5W
DL3-21.8 6W DLE-22.46W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1321.2 lumens
Efficiency: N/A
Efficacy: 63.5 lumens/watt
Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.93
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 20.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P207160

CATALOG NUMBER: LD4B20D010 EU4B10209040 4LBMH1

Luminous Intensity Polar Plot





TEST NUMBER: P207160

CATALOG NUMBER: LD4B20D010 EU4B10209040 4LBMH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	108	105	111	108	106	104	104	102	100		100	99	97		97
2	107	102	98	94	105	100	96	93	97	94	91		94	91	89		91
3	101	94	89	85	99	93	88	84	90	86	83		88	84	82		86
4	96	88	82	77	94	86	81	77	84	80	76		82	78	75		80
5	90	82	75	71	89	81	75	70	79	74	70		77	73	69		75
6	86	76	70	65	84	75	69	65	74	68	64		72	68	64		71
7	81	71	65	60	80	70	64	60	69	64	60		68	63	59		67
8	77	67	60	56	75	66	60	56	65	59	56		64	59	55		63
9	73	63	56	52	72	62	56	52	61	56	52		60	55	52		59
10	69	59	53	49	68	59	53	49	58	52	49		57	52	48		56

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P207160

CATALOG NUMBER: LD4B20D010 EU4B10209040 4LBMH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	120.5	9.1
10°-20°	316.2	23.9
20°-30°	406.4	30.8
30°-40°	305.8	23.1
40°-50°	122.8	9.3
50°-60°	34.9	2.6
60°-70°	11.1	0.8
70°-80°	3.2	0.2
80°-90°	0.3	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	843.2	63.8
0°-40°	1149.0	87.0
0°-60°	1306.7	98.9
0°-90°	1321.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1321.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1310	
5°	1286	121
15°	1129	316
25°	897	406
35°	490	306
45°	152	123
55°	36	35
65°	10	11
75°	2	3
85°	0	0
90°	0	



TEST NUMBER: P207160

CATALOG NUMBER: LD4B20D010 EU4B10209040 4LBMH1

CANDELA DISTRIBUTION (FULL):

	0°
0°	1310.1
2.5°	1302.1
5°	1286.1
7.5°	1256.2
10°	1218.3
12.5°	1172.5
15°	1128.6
17.5°	1078.7
20°	1024.9
22.5°	967.1
25°	897.3
27.5°	813.5
30°	715.8
32.5°	606.2
35°	490.5
37.5°	382.8
40°	287.1
42.5°	211.4
45°	151.5
47.5°	103.7
50°	71.8
52.5°	49.8
55°	35.9
57.5°	25.9
60°	19.9
62.5°	14.0
65°	10.0
67.5°	8.0
70°	6.0
72.5°	4.0
75°	2.0
77.5°	2.0
80°	2.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)