

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P207572

Luminaire Tested: **LD4B20D010 EU4B10209040 4LBMMW1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P207572
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD4B20D010 EU4B10209040 4LBMMW1
Description: PORTFOLIO 4 INCH 50 DEGREE CUTOFF RECESSED DOWNLIGHT
MEDIUM DISTRIBUTION WITH MATTE WHITE TRIM
WATTAGE D010TR-21.86W DE010-20.46W D5LT-21.24W DMX-20.89W DL2-22.5W
DL3-21.8 6W DLE-22.46W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1375.0 lumens
Efficiency: N/A
Efficacy: 66.1 lumens/watt
Spacing Criteria (0/90/45): 0.99 / 0.99 / 0.97
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 20.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P207572

CATALOG NUMBER: LD4B20D010 EU4B10209040 4LBMMW1

Luminous Intensity Polar Plot






TEST NUMBER: P207572

CATALOG NUMBER: LD4B20D010 EU4B10209040 4LBMMW1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	108	105	102	109	106	103	100	102	99	97		98	96	94		94
2	104	98	92	88	102	96	91	87	93	89	85		89	86	83		87
3	97	89	83	77	95	87	82	77	85	80	76		82	78	74		80
4	91	81	74	69	89	80	74	69	78	72	68		76	71	67		74
5	85	75	67	62	83	74	67	62	72	66	61		70	65	61		68
6	80	69	62	56	78	68	61	56	66	60	56		65	59	55		63
7	75	64	57	52	74	63	56	51	62	56	51		60	55	51		59
8	71	59	52	47	69	59	52	47	58	51	47		56	51	47		55
9	67	55	48	44	66	55	48	44	54	48	44		53	47	43		52
10	63	52	45	41	62	51	45	41	51	45	40		50	44	40		49

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P207572

CATALOG NUMBER: LD4B20D010 EU4B10209040 4LBMMW1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	96.8	7.0
10°-20°	259.4	18.9
20°-30°	344.9	25.1
30°-40°	282.1	20.5
40°-50°	164.3	11.9
50°-60°	109.0	7.9
60°-70°	71.7	5.2
70°-80°	37.8	2.8
80°-90°	9.2	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	701.0	51.0
0°-40°	983.0	71.5
0°-60°	1256.3	91.4
0°-90°	1375.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1375.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1044	
5°	1032	97
15°	924	259
25°	757	345
35°	450	282
45°	207	164
55°	122	109
65°	72	72
75°	36	38
85°	8	9
90°	0	



TEST NUMBER: P207572

CATALOG NUMBER: LD4B20D010 EU4B10209040 4LBMMW1

CANDELA DISTRIBUTION (FULL):

	0°
0°	1043.8
2.5°	1041.8
5°	1031.8
7.5°	1007.9
10°	982.0
12.5°	958.1
15°	924.3
17.5°	886.4
20°	854.5
22.5°	810.7
25°	756.9
27.5°	699.2
30°	625.5
32.5°	537.8
35°	450.2
37.5°	370.5
40°	300.8
42.5°	247.0
45°	207.2
47.5°	175.3
50°	153.4
52.5°	135.5
55°	121.5
57.5°	107.6
60°	93.6
62.5°	83.7
65°	71.7
67.5°	61.8
70°	51.8
72.5°	43.8
75°	35.9
77.5°	27.9
80°	19.9
82.5°	13.9
85°	8.0
87.5°	2.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)