

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P207263

Luminaire Tested: **LD4B20D010 EU4B10209040 4LBMWH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P207263
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD4B20D010 EU4B10209040 4LBMWH1
Description: PORTFOLIO 4 INCH 50 DEGREE CUTOFF RECESSED DOWNLIGHT
MEDIUM DISTRIBUTION WITH WHEAT TRIM
WATTAGE D010TR-21.86W DE010-20.46W D5LT-21.24W DMX-20.89W DL2-22.5W
DL3-21.8 6W DLE-22.46W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1349.1 lumens
Efficiency: N/A
Efficacy: 64.9 lumens/watt
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.87
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 20.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P207263

CATALOG NUMBER: LD4B20D010 EU4B10209040 4LBMWH1

Luminous Intensity Polar Plot





TEST NUMBER: P207263

CATALOG NUMBER: LD4B20D010 EU4B10209040 4LBMWH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	111	108	106	111	109	106	105	105	103	101		101	100	98		98
2	108	103	99	96	106	102	98	95	98	95	93		95	93	91		93
3	103	96	91	88	101	95	90	87	92	89	85		90	87	84		88
4	98	90	85	81	96	89	84	80	87	83	79		85	81	78		83
5	93	84	79	74	91	84	78	74	82	77	73		80	76	73		79
6	88	79	73	69	87	79	73	69	77	72	68		76	71	68		74
7	84	75	69	65	82	74	68	64	73	68	64		72	67	64		70
8	80	70	64	60	79	70	64	60	69	64	60		68	63	60		67
9	76	66	61	57	75	66	60	57	65	60	56		64	60	56		63
10	73	63	57	53	72	62	57	53	62	57	53		61	56	53		60

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P207263

CATALOG NUMBER: LD4B20D010 EU4B10209040 4LBMWH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	148.0	11.0
10°-20°	380.6	28.2
20°-30°	446.5	33.1
30°-40°	282.5	20.9
40°-50°	75.7	5.6
50°-60°	10.6	0.8
60°-70°	3.9	0.3
70°-80°	1.3	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	975.0	72.3
0°-40°	1257.6	93.2
0°-60°	1343.9	99.6
0°-90°	1349.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1349.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1602	
5°	1576	148
15°	1363	381
25°	986	446
35°	448	283
45°	86	76
55°	10	11
65°	4	4
75°	2	1
85°	0	0
90°	0	



TEST NUMBER: P207263

CATALOG NUMBER: LD4B20D010 EU4B10209040 4LBMWH1

CANDELA DISTRIBUTION (FULL):

0°	
0°	1602.2
2.5°	1596.2
5°	1576.3
7.5°	1544.4
10°	1498.6
12.5°	1438.8
15°	1363.1
17.5°	1285.4
20°	1191.7
22.5°	1096.0
25°	986.4
27.5°	866.9
30°	733.4
32.5°	587.9
35°	448.4
37.5°	324.8
40°	223.2
42.5°	143.5
45°	85.7
47.5°	47.8
50°	25.9
52.5°	13.9
55°	10.0
57.5°	8.0
60°	6.0
62.5°	6.0
65°	4.0
67.5°	2.0
70°	2.0
72.5°	2.0
75°	2.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)