

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P207462

Luminaire Tested: **LD4B20D010 EU4B10208035 4LBMB1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P207462  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LD4B20D010 EU4B10208035 4LBMB1  
Description: PORTFOLIO 4 INCH 50 DEGREE CUTOFF RECESSED DOWNLIGHT  
MEDIUM DISTRIBUTION WITH SPECULAR BLACK TRIM  
WATTAGE D010TR-21.86W DE010-20.46W D5LT-21.24W DMX-20.89W DL2-22.5W  
DL3-21.8 6W DLE-22.46W  
Light Source: HIGH LUMEN LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 854.4 lumens  
Efficiency: N/A  
Efficacy: 41.1 lumens/watt  
Spacing Criteria (0/90/45): 0.86 / 0.86 / 0.87  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 20.8  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P207462

CATALOG NUMBER: LD4B20D010 EU4B10208035 4LBMB1

### Luminous Intensity Polar Plot





TEST NUMBER: P207462

CATALOG NUMBER: LD4B20D010 EU4B10208035 4LBMB1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |  |     |     |     |  |  |     |     |     |  |  |     |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|--|-----|-----|-----|--|--|-----|-----|-----|--|--|-----|
| RF  | 20  |     |     |     | 20  |     |     |     |  | 20  |     |     |  |  | 20  |     |     |  |  | 20  |
| RC  | 80  |     |     |     | 70  |     |     |     |  | 50  |     |     |  |  | 30  |     |     |  |  | 10  |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  |  | 50  | 30  | 10  |  |  | 50  | 30  | 10  |  |  | 50  |
| RCR |     |     |     |     |     |     |     |     |  |     |     |     |  |  |     |     |     |  |  |     |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 |  | 111 | 111 | 111 |  |  | 106 | 106 | 106 |  |  | 102 |
| 1   | 114 | 111 | 109 | 106 | 111 | 109 | 107 | 105 |  | 105 | 103 | 102 |  |  | 101 | 100 | 99  |  |  | 98  |
| 2   | 108 | 104 | 100 | 96  | 106 | 102 | 98  | 95  |  | 99  | 96  | 93  |  |  | 96  | 93  | 91  |  |  | 93  |
| 3   | 103 | 97  | 92  | 88  | 101 | 95  | 91  | 87  |  | 93  | 89  | 86  |  |  | 90  | 87  | 85  |  |  | 88  |
| 4   | 98  | 91  | 85  | 81  | 96  | 90  | 85  | 81  |  | 87  | 83  | 80  |  |  | 85  | 82  | 79  |  |  | 84  |
| 5   | 93  | 85  | 79  | 75  | 92  | 84  | 79  | 75  |  | 82  | 78  | 74  |  |  | 81  | 77  | 74  |  |  | 79  |
| 6   | 89  | 80  | 74  | 70  | 87  | 79  | 74  | 70  |  | 78  | 73  | 69  |  |  | 76  | 72  | 69  |  |  | 75  |
| 7   | 84  | 75  | 70  | 65  | 83  | 75  | 69  | 65  |  | 73  | 68  | 65  |  |  | 72  | 68  | 65  |  |  | 71  |
| 8   | 80  | 71  | 65  | 61  | 79  | 71  | 65  | 61  |  | 69  | 64  | 61  |  |  | 68  | 64  | 61  |  |  | 67  |
| 9   | 77  | 67  | 61  | 58  | 76  | 67  | 61  | 57  |  | 66  | 61  | 57  |  |  | 65  | 60  | 57  |  |  | 64  |
| 10  | 73  | 64  | 58  | 54  | 72  | 63  | 58  | 54  |  | 62  | 57  | 54  |  |  | 62  | 57  | 54  |  |  | 61  |

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P207462

CATALOG NUMBER: LD4B20D010 EU4B10208035 4LBMB1

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 96.9   | 11.3      |
| 10°-20°   | 241.0  | 28.2      |
| 20°-30°   | 291.4  | 34.1      |
| 30°-40°   | 185.9  | 21.8      |
| 40°-50°   | 38.8   | 4.5       |
| 50°-60°   | 0.5    | 0.1       |
| 60°-70°   | 0.0    | 0.0       |
| 70°-80°   | 0.0    | 0.0       |
| 80°-90°   | 0.0    | 0.0       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-30°    | 629.3  | 73.7      |
| 0°-40°    | 815.1  | 95.4      |
| 0°-60°    | 854.4  | 100.0     |
| 0°-90°    | 854.4  | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 854.4  | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°   | Flux |
|-----|------|------|
| 0°  | 1073 |      |
| 5°  | 1040 | 97   |
| 15° | 860  | 241  |
| 25° | 648  | 291  |
| 35° | 297  | 186  |
| 45° | 40   | 39   |
| 55° | 0    | 1    |
| 65° | 0    | 0    |
| 75° | 0    | 0    |
| 85° | 0    | 0    |
| 90° | 0    |      |



TEST NUMBER: P207462

CATALOG NUMBER: LD4B20D010 EU4B10208035 4LBMB1

**CANDELA DISTRIBUTION (FULL):**

|       | 0°     |
|-------|--------|
| 0°    | 1072.6 |
| 2.5°  | 1060.8 |
| 5°    | 1039.6 |
| 7.5°  | 1008.9 |
| 10°   | 964.1  |
| 12.5° | 909.9  |
| 15°   | 860.4  |
| 17.5° | 810.9  |
| 20°   | 756.7  |
| 22.5° | 704.8  |
| 25°   | 648.3  |
| 27.5° | 572.8  |
| 30°   | 490.3  |
| 32.5° | 393.7  |
| 35°   | 297.0  |
| 37.5° | 207.4  |
| 40°   | 136.7  |
| 42.5° | 80.1   |
| 45°   | 40.1   |
| 47.5° | 16.5   |
| 50°   | 4.7    |
| 52.5° | 0.0    |
| 55°   | 0.0    |
| 57.5° | 0.0    |
| 60°   | 0.0    |
| 62.5° | 0.0    |
| 65°   | 0.0    |
| 67.5° | 0.0    |
| 70°   | 0.0    |
| 72.5° | 0.0    |
| 75°   | 0.0    |
| 77.5° | 0.0    |
| 80°   | 0.0    |
| 82.5° | 0.0    |
| 85°   | 0.0    |
| 87.5° | 0.0    |
| 90°   | 0.0    |



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)