

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P206954

Luminaire Tested: **LD4B20D010 EU4B10209040 4LBWB1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P206954
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD4B20D010 EU4B10209040 4LBWB1
Description: PORTFOLIO 4 INCH 60 DEGREE CUTOFF RECESSED DOWNLIGHT
WIDE DISTRIBUTION WITH SPECULAR BLACK TRIM
WATTAGE D010TR-21.86W DE010-20.46W D5LT-21.24W DMX-20.89W DL2-22.5W
DL3-21.8 6W DLE-22.46W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 858.9 lumens
Efficiency: N/A
Efficacy: 41.3 lumens/watt
Spacing Criteria (0/90/45): 1.08 / 1.08 / 1.03
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 20.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P206954

CATALOG NUMBER: LD4B20D010 EU4B10209040 4LBWB1

Luminous Intensity Polar Plot






TEST NUMBER: P206954

CATALOG NUMBER: LD4B20D010 EU4B10209040 4LBWB1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	108	105	111	108	106	104	104	102	100		100	99	97		97
2	107	102	98	94	105	100	96	93	97	94	91		94	91	89		91
3	101	94	89	85	99	93	88	84	90	86	83		88	84	82		86
4	96	88	82	77	94	86	81	77	84	79	76		82	78	75		80
5	90	81	75	70	89	80	74	70	79	73	69		77	72	69		75
6	85	76	69	65	84	75	69	64	73	68	64		72	67	64		70
7	80	71	64	60	79	70	64	59	69	63	59		67	62	59		66
8	76	66	60	55	75	65	59	55	64	59	55		63	58	54		62
9	72	62	55	51	71	61	55	51	60	55	51		59	54	51		58
10	68	58	52	48	67	58	52	48	57	51	47		56	51	47		55

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P206954

CATALOG NUMBER: LD4B20D010 EU4B10209040 4LBWB1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	67.7	7.9
10°-20°	191.8	22.3
20°-30°	265.1	30.9
30°-40°	227.0	26.4
40°-50°	96.5	11.2
50°-60°	10.8	1.3
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	524.6	61.1
0°-40°	751.6	87.5
0°-60°	858.9	100.0
0°-90°	858.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	858.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	717	
5°	713	68
15°	681	192
25°	582	265
35°	368	227
45°	122	97
55°	6	11
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P206954

CATALOG NUMBER: LD4B20D010 EU4B10209040 4LBWB1

CANDELA DISTRIBUTION (FULL):

	0°
0°	716.9
2.5°	714.9
5°	712.9
7.5°	709.0
10°	701.0
12.5°	697.0
15°	681.1
17.5°	667.1
20°	645.2
22.5°	619.3
25°	581.5
27.5°	539.7
30°	491.9
32.5°	434.1
35°	368.4
37.5°	300.7
40°	233.0
42.5°	173.3
45°	121.5
47.5°	75.7
50°	43.8
52.5°	21.9
55°	6.0
57.5°	0.0
60°	0.0
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)