

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P208292

Luminaire Tested: **LD4B30D010 EU4B30508027 4LBNI1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P208292
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD4B30D010 EU4B30508027 4LBNLI1
Description: PORTFOLIO 4 INCH 50 DEGREE CUTOFF RECESSED DOWNLIGHT
NARROW DISTRIBUTION WITH SPECULAR CLEAR TRIM
WATTAGE D010TR-27.4W DE010-27.95W D5LT-27.65W DMX-27.73W DL2-29.56W
DL3-29.67W DLE-29.73W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2054.9 lumens
Efficiency: N/A
Efficacy: 73.4 lumens/watt
Spacing Criteria (0/90/45): 0.48 / 0.48 / 0.54
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 28
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P208292

CATALOG NUMBER: LD4B30D010 EU4B30508027 4LBNI1

Luminous Intensity Polar Plot





TEST NUMBER: P208292

CATALOG NUMBER: LD4B30D010 EU4B30508027 4LBNI1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	114	112	110	108		112	110	108	106		106	104	103		102	101	100		99	98	97
2	109	105	102	99		107	103	100	98		100	98	95		97	95	93		95	93	92
3	105	99	95	92		103	98	94	91		95	92	89		93	90	88		91	89	87
4	101	94	89	86		99	93	88	85		91	87	84		89	86	83		87	84	82
5	96	89	84	80		95	88	84	80		87	82	79		85	81	79		83	80	78
6	92	85	80	76		91	84	79	76		83	78	75		81	78	75		80	77	74
7	89	81	76	72		88	80	75	72		79	75	71		78	74	71		77	73	71
8	85	77	72	68		84	77	72	68		76	71	68		75	71	68		74	70	67
9	82	74	69	65		81	73	68	65		72	68	65		72	68	65		71	67	64
10	79	71	66	62		78	70	65	62		69	65	62		69	65	62		68	64	62

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P208292

CATALOG NUMBER: LD4B30D010 EU4B30508027 4LBNLI1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	416.7	20.3
10°-20°	713.5	34.7
20°-30°	567.0	27.6
30°-40°	300.1	14.6
40°-50°	51.7	2.5
50°-60°	3.9	0.2
60°-70°	2.0	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1697.2	82.6
0°-40°	1997.4	97.2
0°-60°	2052.9	99.9
0°-90°	2054.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2054.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5288	
5°	4741	417
15°	2579	713
25°	1222	567
35°	475	300
45°	54	52
55°	3	4
65°	3	2
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P208292

CATALOG NUMBER: LD4B30D010 EU4B30508027 4LBNLI1

CANDELA DISTRIBUTION (FULL):

0°	
0°	5288.1
2.5°	5152.0
5°	4740.6
7.5°	4202.6
10°	3633.0
12.5°	3082.4
15°	2579.2
17.5°	2110.8
20°	1737.4
22.5°	1452.6
25°	1221.6
27.5°	1034.8
30°	848.1
32.5°	658.2
35°	474.7
37.5°	313.3
40°	186.7
42.5°	107.6
45°	53.8
47.5°	19.0
50°	6.3
52.5°	6.3
55°	3.2
57.5°	3.2
60°	3.2
62.5°	3.2
65°	3.2
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)