

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P207874

Luminaire Tested: **LD4B20D010 EU4B10208035 4LBNB1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P207874
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD4B20D010 EU4B10208035 4LBNB1
Description: PORTFOLIO 4 INCH 50 DEGREE CUTOFF RECESSED DOWNLIGHT
NARROW DISTRIBUTION WITH SPECULAR BLACK TRIM
WATTAGE D010TR-21.86W DE010-20.46W D5LT-21.24W DMX-20.89W DL2-22.5W
DL3-21.8 6W DLE-22.46W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 805.0 lumens
Efficiency: N/A
Efficacy: 38.7 lumens/watt
Spacing Criteria (0/90/45): 0.62 / 0.62 / 0.79
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 20.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P207874

CATALOG NUMBER: LD4B20D010 EU4B10208035 4LBNB1

Luminous Intensity Polar Plot





TEST NUMBER: P207874

CATALOG NUMBER: LD4B20D010 EU4B10208035 4LBNB1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10		50	30	10			50	30	10			50
RCR																				
0	119	119	119	119	116	116	116	116		111	111	111			106	106	106			102
1	114	111	109	107	111	109	107	105		105	103	102			101	100	99			98
2	109	104	100	97	106	102	99	96		99	96	94			96	94	92			93
3	104	98	93	89	102	96	92	88		94	90	87			91	88	86			89
4	99	92	86	82	97	90	86	82		88	84	81			86	83	80			85
5	94	86	81	77	92	85	80	76		84	79	76			82	78	75			80
6	90	81	76	72	88	81	75	71		79	74	71			78	74	70			76
7	86	77	71	67	84	76	71	67		75	70	67			74	69	66			73
8	82	73	67	63	80	72	67	63		71	66	63			70	66	62			69
9	78	69	63	60	77	68	63	59		67	63	59			67	62	59			66
10	75	65	60	56	74	65	60	56		64	59	56			63	59	56			63

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P207874

CATALOG NUMBER: LD4B20D010 EU4B10208035 4LBNB1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	109.7	13.6
10°-20°	232.6	28.9
20°-30°	269.9	33.5
30°-40°	169.0	21.0
40°-50°	23.8	3.0
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	612.2	76.0
0°-40°	781.2	97.0
0°-60°	805.0	100.0
0°-90°	805.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	805.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1316	
5°	1220	110
15°	826	233
25°	596	270
35°	271	169
45°	21	24
55°	0	0
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P207874

CATALOG NUMBER: LD4B20D010 EU4B10208035 4LBNB1

CANDELA DISTRIBUTION (FULL):

0°	
0°	1316.3
2.5°	1290.4
5°	1219.8
7.5°	1118.5
10°	1014.9
12.5°	916.0
15°	826.5
17.5°	751.2
20°	694.7
22.5°	642.9
25°	595.8
27.5°	539.2
30°	466.2
32.5°	374.4
35°	270.8
37.5°	176.6
40°	101.3
42.5°	51.8
45°	21.2
47.5°	4.7
50°	0.0
52.5°	0.0
55°	0.0
57.5°	0.0
60°	0.0
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)