

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P208506

Luminaire Tested: **LD4B30D010 EU4B30509040 4LBNWH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P208506
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD4B30D010 EU4B30509040 4LBNWH1
Description: PORTFOLIO 4 INCH 50 DEGREE CUTOFF RECESSED DOWNLIGHT
NARROW DISTRIBUTION WITH WHEAT TRIM
WATTAGE D010TR-27.4W DE010-27.95W D5LT-27.65W DMX-27.73W DL2-29.56W
DL3-29.67W DLE-29.73W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1662.9 lumens
Efficiency: N/A
Efficacy: 59.4 lumens/watt
Spacing Criteria (0/90/45): 0.53 / 0.53 / 0.62
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 28
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P208506

CATALOG NUMBER: LD4B30D010 EU4B30509040 4LBNWH1

Luminous Intensity Polar Plot






TEST NUMBER: P208506

CATALOG NUMBER: LD4B30D010 EU4B30509040 4LBNWH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10		50	30	10			50	30	10			0
RCR																				
0	119	119	119	119	116	116	116	116		111	111	111			106	106	106			100
1	114	111	109	107	112	109	107	105		105	104	102			102	100	99			95
2	109	105	101	98	107	103	100	97		100	97	95			97	95	93			89
3	104	98	94	90	102	97	93	90		94	91	88			92	89	87			84
4	100	93	88	84	98	92	87	83		90	86	82			88	84	82			79
5	95	88	82	78	94	87	82	78		85	81	77			83	80	77			75
6	91	83	78	74	90	82	77	74		81	76	73			79	76	73			71
7	87	79	73	70	86	78	73	69		77	72	69			76	72	69			67
8	84	75	70	66	82	74	69	66		73	69	65			72	68	65			64
9	80	71	66	62	79	71	66	62		70	65	62			69	65	62			61
10	77	68	63	59	76	68	63	59		67	62	59			66	62	59			58

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P208506

CATALOG NUMBER: LD4B30D010 EU4B30509040 4LBNWH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	289.0	17.4
10°-20°	542.1	32.6
20°-30°	486.4	29.3
30°-40°	279.1	16.8
40°-50°	55.7	3.3
50°-60°	7.0	0.4
60°-70°	3.2	0.2
70°-80°	0.4	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1317.5	79.2
0°-40°	1596.6	96.0
0°-60°	1659.3	99.8
0°-90°	1662.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1662.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3534	
5°	3250	289
15°	1946	542
25°	1051	486
35°	442	279
45°	60	56
55°	9	7
65°	3	3
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P208506

CATALOG NUMBER: LD4B30D010 EU4B30509040 4LBNWH1

CANDELA DISTRIBUTION (FULL):

	0°
0°	3534.1
2.5°	3462.3
5°	3249.9
7.5°	2939.8
10°	2601.1
12.5°	2268.0
15°	1946.5
17.5°	1665.1
20°	1424.0
22.5°	1223.0
25°	1050.8
27.5°	913.0
30°	760.8
32.5°	605.8
35°	442.1
37.5°	301.4
40°	186.6
42.5°	112.0
45°	60.3
47.5°	25.8
50°	11.5
52.5°	8.6
55°	8.6
57.5°	5.7
60°	5.7
62.5°	2.9
65°	2.9
67.5°	2.9
70°	2.9
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)