

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P205830

Luminaire Tested: **LD4B30D010 EU4B30509050 4LBSWH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P205830
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD4B30D010 EU4B30509050 4LBSWH1
Description: PORTFOLIO 4 INCH SHALLOW RECESSED DOWNLIGHT
SHALLOW DISTRIBUTION WITH WHEAT TRIM
WATTAGE D010TR-27.4W DE010-27.95W D5LT-27.65W DMX-27.73W DL2-29.56W
DL3-29.67W DLE-29.73W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2511.4 lumens
Efficiency: N/A
Efficacy: 89.7 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 1.08
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 28
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P205830

CATALOG NUMBER: LD4B30D010 EU4B30509050 4LBSWH1

Luminous Intensity Polar Plot





TEST NUMBER: P205830

CATALOG NUMBER: LD4B30D010 EU4B30509050 4LBSWH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	111	107	104	101	108	105	102	99	101	98	96		97	95	93		94
2	103	96	90	85	100	94	89	84	91	86	83		87	84	81		85
3	95	86	79	73	93	84	78	73	82	76	72		79	74	70		76
4	88	77	70	64	86	76	69	63	74	68	63		72	66	62		69
5	81	70	62	56	79	69	62	56	67	60	55		65	59	55		63
6	76	64	56	50	74	63	55	50	61	54	49		60	54	49		58
7	71	58	51	45	69	58	50	45	56	49	45		55	49	44		54
8	66	54	46	41	65	53	46	41	52	45	40		51	45	40		50
9	62	50	42	37	61	49	42	37	48	41	37		47	41	37		46
10	58	46	39	34	57	46	39	34	45	38	34		44	38	34		43

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P205830

CATALOG NUMBER: LD4B30D010 EU4B30509050 4LB5WH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	138.1	5.5
10°-20°	357.6	14.2
20°-30°	467.7	18.6
30°-40°	495.2	19.7
40°-50°	461.9	18.4
50°-60°	349.8	13.9
60°-70°	189.5	7.5
70°-80°	50.8	2.0
80°-90°	0.7	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	963.4	38.4
0°-40°	1458.6	58.1
0°-60°	2270.4	90.4
0°-90°	2511.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2511.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1498	
5°	1476	138
15°	1278	358
25°	1017	468
35°	792	495
45°	602	462
55°	393	350
65°	190	189
75°	44	51
85°	0	1
90°	0	



TEST NUMBER: P205830

CATALOG NUMBER: LD4B30D010 EU4B30509050 4LBSWH1

CANDELA DISTRIBUTION (FULL):

0°	
0°	1497.8
2.5°	1492.3
5°	1475.8
7.5°	1440.1
10°	1393.4
12.5°	1338.4
15°	1277.9
17.5°	1209.2
20°	1148.8
22.5°	1080.1
25°	1016.9
27.5°	953.6
30°	893.2
32.5°	841.0
35°	791.5
37.5°	742.0
40°	695.3
42.5°	648.6
45°	601.9
47.5°	549.7
50°	497.4
52.5°	445.2
55°	393.0
57.5°	338.0
60°	285.8
62.5°	236.4
65°	189.6
67.5°	145.7
70°	107.2
72.5°	74.2
75°	44.0
77.5°	19.2
80°	5.5
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)