

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P206844

Luminaire Tested: **LD4B20D010 EU4B10208035 4LBWGPH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P206844
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD4B20D010 EU4B10208035 4LBWGPH1
Description: PORTFOLIO 4 INCH 60 DEGREE CUTOFF RECESSED DOWNLIGHT
WIDE DISTRIBUTIONWITH GRAPHITE HAZE TRIM
WATTAGE D010TR-21.86W DE010-20.46W D5LT-21.24W DMX-20.89W DL2-22.5W
DL3-21.8 6W DLE-22.46W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1358.2 lumens
Efficiency: N/A
Efficacy: 65.3 lumens/watt
Spacing Criteria (0/90/45): 1.12 / 1.12 / 1.08
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 20.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P206844

CATALOG NUMBER: LD4B20D010 EU4B10208035 4LBWGPH1

Luminous Intensity Polar Plot






TEST NUMBER: P206844

CATALOG NUMBER: LD4B20D010 EU4B10208035 4LBWGPH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	107	104	110	107	105	103	103	101	99		100	98	96		96
2	106	100	96	92	104	99	95	91	95	92	89		92	90	87		90
3	100	92	87	82	98	91	86	81	88	84	80		86	82	79		83
4	94	85	78	74	92	84	78	73	81	76	72		79	75	71		77
5	88	78	72	67	86	77	71	66	75	70	66		74	69	65		72
6	83	72	65	61	81	71	65	60	70	64	60		68	63	59		67
7	78	67	60	55	76	66	60	55	65	59	55		64	58	55		63
8	73	62	56	51	72	62	55	51	61	55	50		59	54	50		58
9	69	58	51	47	68	58	51	47	57	51	47		56	50	46		55
10	65	54	48	43	64	54	48	43	53	47	43		52	47	43		51

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P206844

CATALOG NUMBER: LD4B20D010 EU4B10208035 4LBWGPH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	92.2	6.8
10°-20°	261.3	19.2
20°-30°	374.7	27.6
30°-40°	352.9	26.0
40°-50°	194.9	14.3
50°-60°	62.5	4.6
60°-70°	15.6	1.2
70°-80°	3.8	0.3
80°-90°	0.3	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	728.3	53.6
0°-40°	1081.1	79.6
0°-60°	1338.5	98.5
0°-90°	1358.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1358.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	978	
5°	973	92
15°	926	261
25°	822	375
35°	572	353
45°	247	195
55°	64	63
65°	14	16
75°	2	4
85°	0	0
90°	0	



TEST NUMBER: P206844

CATALOG NUMBER: LD4B20D010 EU4B10208035 4LBWGPH1

CANDELA DISTRIBUTION (FULL):

	0°
0°	977.5
2.5°	970.5
5°	972.8
7.5°	965.8
10°	954.0
12.5°	942.2
15°	925.7
17.5°	911.6
20°	888.0
22.5°	855.1
25°	822.1
27.5°	777.3
30°	718.4
32.5°	652.5
35°	572.4
37.5°	487.6
40°	400.4
42.5°	320.4
45°	247.3
47.5°	186.1
50°	134.3
52.5°	94.2
55°	63.6
57.5°	42.4
60°	30.6
62.5°	21.2
65°	14.1
67.5°	9.4
70°	7.1
72.5°	4.7
75°	2.4
77.5°	2.4
80°	2.4
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)