

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P207050

Luminaire Tested: **LD4B20D010 EU4B10208035 4LBWMW1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P207050
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD4B20D010 EU4B10208035 4LBWMW1
Description: PORTFOLIO 4 INCH 60 DEGREE CUTOFF RECESSED DOWNLIGHT
WIDE DISTRIBUTION WITH MATTE WHITE TRIM
WATTAGE D010TR-21.86W DE010-20.46W D5LT-21.24W DMX-20.89W DL2-22.5W
DL3-21.8 6W DLE-22.46W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1812.5 lumens
Efficiency: N/A
Efficacy: 87.1 lumens/watt
Spacing Criteria (0/90/45): 1.1 / 1.1 / 1.09
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 20.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P207050

CATALOG NUMBER: LD4B20D010 EU4B10208035 4LBWMW1

Luminous Intensity Polar Plot





TEST NUMBER: P207050

CATALOG NUMBER: LD4B20D010 EU4B10208035 4LBWMW1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20				20
RC	80				70					50					30				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	0
RCR																			
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90	88	
2	103	96	91	86	101	94	89	85	91	87	83	88	84	81	85	82	80	78	
3	96	87	80	75	93	85	79	74	83	77	73	80	76	72	78	74	71	69	
4	89	79	72	66	87	78	71	66	75	69	65	73	68	64	71	67	63	61	
5	83	72	64	59	81	71	64	58	69	63	58	67	62	57	65	61	57	55	
6	78	66	58	53	76	65	58	53	64	57	52	62	56	52	60	55	51	50	
7	73	61	53	48	71	60	53	48	59	52	47	57	51	47	56	51	47	45	
8	68	56	49	44	67	56	49	44	54	48	43	53	47	43	52	47	43	41	
9	64	52	45	40	63	52	45	40	51	44	40	50	44	40	49	43	39	38	
10	61	49	42	37	59	48	41	37	47	41	37	46	41	37	46	40	36	35	

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P207050

CATALOG NUMBER: LD4B20D010 EU4B10208035 4LBWMW1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	103.1	5.7
10°-20°	288.4	15.9
20°-30°	407.6	22.5
30°-40°	394.8	21.8
40°-50°	266.4	14.7
50°-60°	165.3	9.1
60°-70°	110.5	6.1
70°-80°	60.4	3.3
80°-90°	16.0	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	799.1	44.1
0°-40°	1193.8	65.9
0°-60°	1625.5	89.7
0°-90°	1812.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1812.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1098	
5°	1089	103
15°	1023	288
25°	894	408
35°	635	395
45°	341	266
55°	181	165
65°	110	110
75°	56	60
85°	14	16
90°	0	



TEST NUMBER: P207050

CATALOG NUMBER: LD4B20D010 EU4B10208035 4LBWMW1

CANDELA DISTRIBUTION (FULL):

	0°
0°	1098.3
2.5°	1098.3
5°	1088.9
7.5°	1077.2
10°	1063.0
12.5°	1048.9
15°	1023.1
17.5°	1001.9
20°	966.6
22.5°	931.3
25°	893.7
27.5°	842.0
30°	785.5
32.5°	712.6
35°	635.0
37.5°	557.4
40°	479.8
42.5°	402.2
45°	341.0
47.5°	284.6
50°	242.2
52.5°	207.0
55°	181.1
57.5°	159.9
60°	143.5
62.5°	127.0
65°	110.5
67.5°	96.4
70°	82.3
72.5°	70.6
75°	56.4
77.5°	44.7
80°	32.9
82.5°	23.5
85°	14.1
87.5°	4.7
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)