

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P206741

Luminaire Tested: **LD4B20D010 EU4B10208035 4LBWWH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P206741
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD4B20D010 EU4B10208035 4LBWWH1
Description: PORTFOLIO 4 INCH 60 DEGREE CUTOFF RECESSED DOWNLIGHT
WIDE DISTRIBUTION WITH WHEAT TRIM
WATTAGE D010TR-21.86W DE010-20.46W D5LT-21.24W DMX-20.89W DL2-22.5W
DL3-21.8 6W DLE-22.46W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1800.8 lumens
Efficiency: N/A
Efficacy: 86.6 lumens/watt
Spacing Criteria (0/90/45): 1.26 / 1.26 / 1.16
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 20.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P206741

CATALOG NUMBER: LD4B20D010 EU4B10208035 4LBWWH1

Luminous Intensity Polar Plot





TEST NUMBER: P206741

CATALOG NUMBER: LD4B20D010 EU4B10208035 4LBWWH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	107	104	110	107	105	103	103	101	100		100	98	97		96
2	106	101	96	92	104	99	95	91	96	92	89		93	90	87		90
3	100	93	87	82	98	91	86	82	88	84	80		86	82	79		84
4	94	85	79	74	92	84	78	74	82	77	73		80	75	72		78
5	88	79	72	67	86	78	71	67	76	70	66		74	69	65		72
6	83	73	66	61	81	72	65	61	70	64	60		69	64	60		67
7	78	67	60	56	76	67	60	55	65	59	55		64	59	55		63
8	73	62	56	51	72	62	55	51	61	55	51		60	54	50		59
9	69	58	51	47	68	58	51	47	57	51	47		56	50	47		55
10	65	54	48	43	64	54	48	43	53	47	43		52	47	43		51

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P206741

CATALOG NUMBER: LD4B20D010 EU4B10208035 4LBWWH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	109.1	6.1
10°-20°	337.5	18.7
20°-30°	519.1	28.8
30°-40°	500.9	27.8
40°-50°	261.2	14.5
50°-60°	55.0	3.1
60°-70°	12.8	0.7
70°-80°	5.0	0.3
80°-90°	0.3	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	965.7	53.6
0°-40°	1466.5	81.4
0°-60°	1782.7	99.0
0°-90°	1800.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1800.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1126	
5°	1135	109
15°	1194	337
25°	1138	519
35°	813	501
45°	332	261
55°	50	55
65°	12	13
75°	5	5
85°	0	0
90°	0	



TEST NUMBER: P206741

CATALOG NUMBER: LD4B20D010 EU4B10208035 4LBWWH1

CANDELA DISTRIBUTION (FULL):

0°	
0°	1125.9
2.5°	1128.2
5°	1135.3
7.5°	1144.7
10°	1158.9
12.5°	1177.7
15°	1194.2
17.5°	1203.6
20°	1196.6
22.5°	1182.4
25°	1137.7
27.5°	1083.5
30°	1012.8
32.5°	918.6
35°	812.6
37.5°	697.2
40°	577.1
42.5°	457.0
45°	332.1
47.5°	223.8
50°	143.7
52.5°	87.2
55°	49.5
57.5°	30.6
60°	21.2
62.5°	16.5
65°	11.8
67.5°	9.4
70°	7.1
72.5°	7.1
75°	4.7
77.5°	2.4
80°	2.4
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)