

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P1500392

Luminaire Tested: LD4C25D010 EU4259030 4LBMH

Issue Date: 2/8/2022

Test Information

Test Method: LM-79-2019
Report Number: P1500392
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P207151)
Test Lab: INNOVATION CENTER
Issue Date: 2/8/2022
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4C25D010 EU4259030 4LBMH
Description: 4 INCH 2500 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 3000K, 90CRI LEDS AND 4LBM TRIM FINISH
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1881.9 lumens
Efficiency: N/A
Efficacy: 59.7 lumens/watt
Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.93
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 31.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1500392

CATALOG NUMBER: LD4C25D010 EU4259030 4LBMH

Luminous Intensity Polar Plot



TEST NUMBER: P1500392

CATALOG NUMBER: LD4C25D010 EU4259030 4LBMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	108	105	111	108	106	104	104	102	100		100	99	97		97
2	107	102	98	94	105	100	96	93	97	94	91		94	91	89		91
3	101	94	89	85	99	93	88	84	90	86	83		88	84	82		86
4	96	88	82	77	94	86	81	77	84	80	76		82	78	75		80
5	90	82	75	71	89	81	75	70	79	74	70		77	73	69		75
6	86	76	70	65	84	75	69	65	74	68	64		72	68	64		71
7	81	71	65	60	80	70	64	60	69	64	60		68	63	59		67
8	77	67	60	56	75	66	60	56	65	59	56		64	59	55		63
9	73	63	56	52	72	62	56	52	61	56	52		60	55	52		59
10	69	59	53	49	68	59	53	49	58	52	49		57	52	48		56

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	229257
5°	225927
10°	216489
15°	204479
20°	190864
25°	173265
30°	144654
35°	104804
40°	65609
45°	37493
50°	19552
55°	10945
60°	6978
65°	4128
70°	3053
75°	1329
80°	1981
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 37493 cd/sqm

TEST NUMBER: P1500392

CATALOG NUMBER: LD4C25D010 EU4259030 4LBMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	171.7	9.1
10°-20°	450.5	23.9
20°-30°	578.9	30.8
30°-40°	435.6	23.1
40°-50°	175.0	9.3
50°-60°	49.7	2.6
60°-70°	15.8	0.8
70°-80°	4.5	0.2
80°-90°	0.4	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1201.1	63.8
0°-40°	1636.7	87.0
0°-60°	1861.4	98.9
0°-90°	1881.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1881.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1866	
5°	1832	172
15°	1608	450
25°	1278	579
35°	699	436
45°	216	175
55°	51	50
65°	14	16
75°	3	4
85°	0	0
90°	0	

TEST NUMBER: P1500392

CATALOG NUMBER: LD4C25D010 EU4259030 4LBMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	1866.1
2.5°	1854.8
5°	1832.0
7.5°	1789.4
10°	1735.4
12.5°	1670.2
15°	1607.7
17.5°	1536.6
20°	1459.9
22.5°	1377.6
25°	1278.2
27.5°	1158.8
30°	1019.7
32.5°	863.4
35°	698.8
37.5°	545.3
40°	409.1
42.5°	301.1
45°	215.8
47.5°	147.8
50°	102.3
52.5°	71.0
55°	51.1
57.5°	36.9
60°	28.4
62.5°	19.9
65°	14.2
67.5°	11.4
70°	8.5
72.5°	5.7
75°	2.8
77.5°	2.8
80°	2.8
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)