

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P1500405

Luminaire Tested: LD4C35D010 EU4359050 4LBMH

Issue Date: 2/8/2022

Test Information

Test Method: LM-79-2019
Report Number: P1500405
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P207151)
Test Lab: INNOVATION CENTER
Issue Date: 2/8/2022
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4C35D010 EU4359050 4LBMH
Description: 4 INCH 3500 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 5000K, 90CRI LEDS AND 4LBM TRIM FINISH
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2703.0 lumens
Efficiency: N/A
Efficacy: 66.9 lumens/watt
Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.93
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 40.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1500405

CATALOG NUMBER: LD4C35D010 EU4359050 4LBMH

Luminous Intensity Polar Plot



TEST NUMBER: P1500405

CATALOG NUMBER: LD4C35D010 EU4359050 4LBMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	108	105	111	108	106	104	104	102	100		100	99	97		97
2	107	102	98	94	105	100	96	93	97	94	91		94	91	89		91
3	101	94	89	85	99	93	88	84	90	86	83		88	84	82		86
4	96	88	82	77	94	86	81	77	84	80	76		82	78	75		80
5	90	82	75	71	89	81	75	70	79	74	70		77	73	69		75
6	86	76	70	65	84	75	69	65	74	68	64		72	68	64		71
7	81	71	65	60	80	70	64	60	69	64	60		68	63	59		67
8	77	67	60	56	75	66	60	56	65	59	56		64	59	55		63
9	73	63	56	52	72	62	56	52	61	56	52		60	55	52		59
10	69	59	53	49	68	59	53	49	58	52	49		57	52	48		56

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	329272
5°	324487
10°	310936
15°	293675
20°	274131
25°	248850
30°	207767
35°	150516
40°	94220
45°	53860
50°	28076
55°	15743
60°	10025
65°	5930
70°	4382
75°	1946
80°	2901
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 53860 cd/sqm

TEST NUMBER: P1500405

CATALOG NUMBER: LD4C35D010 EU4359050 4LBMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	246.6	9.1
10°-20°	647.0	23.9
20°-30°	831.5	30.8
30°-40°	625.6	23.1
40°-50°	251.3	9.3
50°-60°	71.4	2.6
60°-70°	22.6	0.8
70°-80°	6.5	0.2
80°-90°	0.6	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1725.1	63.8
0°-40°	2350.7	87.0
0°-60°	2673.4	98.9
0°-90°	2703.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2703.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2680	
5°	2631	247
15°	2309	647
25°	1836	832
35°	1004	626
45°	310	251
55°	74	71
65°	20	23
75°	4	6
85°	0	1
90°	0	

TEST NUMBER: P1500405

CATALOG NUMBER: LD4C35D010 EU4359050 4LBMH

CANDELA DISTRIBUTION (FULL):

	0°
0°	2680.2
2.5°	2663.9
5°	2631.2
7.5°	2570.0
10°	2492.5
12.5°	2398.8
15°	2309.0
17.5°	2207.0
20°	2096.8
22.5°	1978.6
25°	1835.8
27.5°	1664.4
30°	1464.6
32.5°	1240.1
35°	1003.6
37.5°	783.2
40°	587.5
42.5°	432.4
45°	310.0
47.5°	212.2
50°	146.9
52.5°	102.0
55°	73.5
57.5°	53.1
60°	40.8
62.5°	28.6
65°	20.4
67.5°	16.3
70°	12.2
72.5°	8.2
75°	4.1
77.5°	4.1
80°	4.1
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)