

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P205711

Luminaire Tested: **LD4B20D010 EU4B10209035 4LBSH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P205711
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD4B20D010 EU4B10209035 4LBSH1
Description: PORTFOLIO 4 INCH SHALLOW RECESSED DOWNLIGHT
SHALLOW DISTRIBUTION WITH SEMI-SPECULAR CLEAR TRIM
WATTAGE D010TR-21.86W DE010-20.46W D5LT-21.24W DMX-20.89W DL2-22.5W
DL3-21.8 6W DLE-22.46W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1723.1 lumens
Efficiency: N/A
Efficacy: 82.8 lumens/watt
Spacing Criteria (0/90/45): 1.06 / 1.06 / 1.17
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 20.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P205711

CATALOG NUMBER: LD4B20D010 EU4B10209035 4LBSH1

Luminous Intensity Polar Plot






TEST NUMBER: P205711

CATALOG NUMBER: LD4B20D010 EU4B10209035 4LBSH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90	88		
2	102	96	90	85	100	94	88	84	90	86	82	87	83	80	84	81	79	77		
3	95	85	78	73	92	84	77	72	81	75	71	78	74	70	76	72	69	67		
4	87	77	69	63	85	75	68	63	73	67	62	71	65	61	69	64	60	58		
5	81	69	61	55	79	68	61	55	66	60	55	64	59	54	63	58	53	51		
6	75	63	55	49	73	62	54	49	60	54	49	59	53	48	57	52	48	46		
7	70	58	50	44	68	57	49	44	55	49	44	54	48	43	53	47	43	41		
8	65	53	45	40	64	52	45	40	51	44	39	50	44	39	49	43	39	37		
9	61	49	41	36	60	48	41	36	47	40	36	46	40	36	45	40	35	34		
10	58	45	38	33	56	45	38	33	44	37	33	43	37	33	42	37	33	31		

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P205711

CATALOG NUMBER: LD4B20D010 EU4B10209035 4LBSH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	84.4	4.9
10°-20°	229.4	13.3
20°-30°	318.6	18.5
30°-40°	347.7	20.2
40°-50°	324.3	18.8
50°-60°	246.2	14.3
60°-70°	134.8	7.8
70°-80°	37.1	2.2
80°-90°	0.5	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	632.5	36.7
0°-40°	980.1	56.9
0°-60°	1550.7	90.0
0°-90°	1723.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1723.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	901	
5°	894	84
15°	818	229
25°	692	319
35°	556	348
45°	421	324
55°	275	246
65°	135	135
75°	32	37
85°	0	1
90°	0	



TEST NUMBER: P205711

CATALOG NUMBER: LD4B20D010 EU4B10209035 4LBSH1

CANDELA DISTRIBUTION (FULL):

	0°
0°	901.2
2.5°	901.2
5°	893.6
7.5°	882.2
10°	865.1
12.5°	842.4
15°	817.7
17.5°	787.3
20°	758.9
22.5°	724.7
25°	692.5
27.5°	660.2
30°	624.2
32.5°	590.0
35°	555.9
37.5°	521.7
40°	489.5
42.5°	455.3
45°	421.2
47.5°	387.0
50°	349.1
52.5°	313.0
55°	275.1
57.5°	239.0
60°	203.0
62.5°	167.0
65°	134.7
67.5°	104.3
70°	77.8
72.5°	53.1
75°	32.3
77.5°	15.2
80°	3.8
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)