

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P1500435

Luminaire Tested: LD4C65D010 EU4659050 4LBMH

Issue Date: 2/8/2022

Test Information

Test Method: LM-79-2019
Report Number: P1500435
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P207151)
Test Lab: INNOVATION CENTER
Issue Date: 2/8/2022
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4C65D010 EU4659050 4LBMH
Description: 4 INCH 6500 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 5000K, 90CRI LEDS AND 4LBM TRIM FINISH
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5198.9 lumens
Efficiency: N/A
Efficacy: 71.8 lumens/watt
Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.93
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 72.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1500435

CATALOG NUMBER: LD4C65D010 EU4659050 4LBMH

Luminous Intensity Polar Plot



TEST NUMBER: P1500435

CATALOG NUMBER: LD4C65D010 EU4659050 4LBMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	108	105	111	108	106	104	104	102	100		100	99	97		97
2	107	102	98	94	105	100	96	93	97	94	91		94	91	89		91
3	101	94	89	85	99	93	88	84	90	86	83		88	84	82		86
4	96	88	82	77	94	86	81	77	84	80	76		82	78	75		80
5	90	82	75	71	89	81	75	70	79	74	70		77	73	69		75
6	86	76	70	65	84	75	69	65	74	68	64		72	68	64		71
7	81	71	65	60	80	70	64	60	69	64	60		68	63	59		67
8	77	67	60	56	75	66	60	56	65	59	56		64	59	55		63
9	73	63	56	52	72	62	56	52	61	56	52		60	55	52		59
10	69	59	53	49	68	59	53	49	58	52	49		57	52	48		56

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	633322
5°	624124
10°	598045
15°	564864
20°	527266
25°	478641
30°	399617
35°	289499
40°	181222
45°	103584
50°	54012
55°	30265
60°	19288
65°	11395
70°	8441
75°	3702
80°	5518
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 103584 cd/sqm

TEST NUMBER: P1500435

CATALOG NUMBER: LD4C65D010 EU4659050 4LBMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	474.3	9.1
10°-20°	1244.4	23.9
20°-30°	1599.3	30.8
30°-40°	1203.3	23.1
40°-50°	483.3	9.3
50°-60°	137.4	2.6
60°-70°	43.5	0.8
70°-80°	12.4	0.2
80°-90°	1.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3318.1	63.8
0°-40°	4521.4	87.0
0°-60°	5142.0	98.9
0°-90°	5198.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5198.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5155	
5°	5061	474
15°	4441	1244
25°	3531	1599
35°	1930	1203
45°	596	483
55°	141	137
65°	39	43
75°	8	12
85°	0	1
90°	0	

TEST NUMBER: P1500435

CATALOG NUMBER: LD4C65D010 EU4659050 4LBMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	5155.1
2.5°	5123.7
5°	5060.9
7.5°	4943.2
10°	4794.0
12.5°	4613.9
15°	4441.2
17.5°	4244.9
20°	4033.0
22.5°	3805.7
25°	3531.0
27.5°	3201.3
30°	2817.0
32.5°	2385.2
35°	1930.3
37.5°	1506.4
40°	1130.0
42.5°	831.7
45°	596.2
47.5°	408.2
50°	282.6
52.5°	196.2
55°	141.3
57.5°	102.0
60°	78.5
62.5°	54.9
65°	39.2
67.5°	31.4
70°	23.5
72.5°	15.7
75°	7.8
77.5°	7.8
80°	7.8
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)