

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P1500438

Luminaire Tested: LD4C70D010 EU4709035 4LBMH

Issue Date: 2/8/2022

Test Information

Test Method: LM-79-2019
Report Number: P1500438
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P207151)
Test Lab: INNOVATION CENTER
Issue Date: 2/8/2022
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4C70D010 EU4709035 4LBMH
Description: 4 INCH 7000 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 3500K, 90CRI LEDS AND 4LBM TRIM FINISH
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5343.0 lumens
Efficiency: N/A
Efficacy: 68.5 lumens/watt
Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.93
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 78
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1500438

CATALOG NUMBER: LD4C70D010 EU4709035 4LBMH

Luminous Intensity Polar Plot



TEST NUMBER: P1500438

CATALOG NUMBER: LD4C70D010 EU4709035 4LBMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	108	105	111	108	106	104	104	102	100		100	99	97		97
2	107	102	98	94	105	100	96	93	97	94	91		94	91	89		91
3	101	94	89	85	99	93	88	84	90	86	83		88	84	82		86
4	96	88	82	77	94	86	81	77	84	80	76		82	78	75		80
5	90	82	75	71	89	81	75	70	79	74	70		77	73	69		75
6	86	76	70	65	84	75	69	65	74	68	64		72	68	64		71
7	81	71	65	60	80	70	64	60	69	64	60		68	63	59		67
8	77	67	60	56	75	66	60	56	65	59	56		64	59	55		63
9	73	63	56	52	72	62	56	52	61	56	52		60	55	52		59
10	69	59	53	49	68	59	53	49	58	52	49		57	52	48		56

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	650865
5°	641414
10°	614612
15°	580508
20°	541870
25°	491884
30°	410682
35°	297523
40°	186242
45°	106451
50°	55503
55°	31100
60°	19829
65°	11715
70°	8693
75°	3845
80°	5731
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 106451 cd/sqm

TEST NUMBER: P1500438

CATALOG NUMBER: LD4C70D010 EU4709035 4LBMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	487.5	9.1
10°-20°	1278.9	23.9
20°-30°	1643.6	30.8
30°-40°	1236.6	23.1
40°-50°	496.7	9.3
50°-60°	141.2	2.6
60°-70°	44.7	0.8
70°-80°	12.7	0.2
80°-90°	1.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3410.0	63.8
0°-40°	4646.6	87.0
0°-60°	5284.5	98.9
0°-90°	5343.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5343.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5298	
5°	5201	487
15°	4564	1279
25°	3629	1644
35°	1984	1237
45°	613	497
55°	145	141
65°	40	45
75°	8	13
85°	0	1
90°	0	

TEST NUMBER: P1500438

CATALOG NUMBER: LD4C70D010 EU4709035 4LBMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	5297.9
2.5°	5265.6
5°	5201.1
7.5°	5080.1
10°	4926.8
12.5°	4741.6
15°	4564.2
17.5°	4362.5
20°	4144.7
22.5°	3911.1
25°	3628.7
27.5°	3289.9
30°	2895.0
32.5°	2451.3
35°	1983.8
37.5°	1548.2
40°	1161.3
42.5°	854.8
45°	612.7
47.5°	419.5
50°	290.4
52.5°	201.7
55°	145.2
57.5°	104.9
60°	80.7
62.5°	56.5
65°	40.3
67.5°	32.3
70°	24.2
72.5°	16.1
75°	8.1
77.5°	8.1
80°	8.1
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)