

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P1500370

Luminaire Tested: LD4C08D010 EU4089050 4LBMH

Issue Date: 2/8/2022

Test Information

Test Method: LM-79-2019
Report Number: P1500370
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P207151)
Test Lab: INNOVATION CENTER
Issue Date: 2/8/2022
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4C08D010 EU4089050 4LBMH
Description: 4 INCH 800 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 5000K, 90CRI LEDS AND 4LBM TRIM ' FINISH
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 685.0 lumens
Efficiency: N/A
Efficacy: 69.2 lumens/watt
Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.93
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 9.9
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1500370

CATALOG NUMBER: LD4C08D010 EU4089050 4LBMH

Luminous Intensity Polar Plot



TEST NUMBER: P1500370

CATALOG NUMBER: LD4C08D010 EU4089050 4LBMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	108	105	111	108	106	104	104	102	100		100	99	97		97
2	107	102	98	94	105	100	96	93	97	94	91		94	91	89		91
3	101	94	89	85	99	93	88	84	90	86	83		88	84	82		86
4	96	88	82	77	94	86	81	77	84	80	76		82	78	75		80
5	90	82	75	71	89	81	75	70	79	74	70		77	73	69		75
6	86	76	70	65	84	75	69	65	74	68	64		72	68	64		71
7	81	71	65	60	80	70	64	60	69	64	60		68	63	59		67
8	77	67	60	56	75	66	60	56	65	59	56		64	59	55		63
9	73	63	56	52	72	62	56	52	61	56	52		60	55	52		59
10	69	59	53	49	68	59	53	49	58	52	49		57	52	48		56

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	83442
5°	82232
10°	78791
15°	74430
20°	69474
25°	63060
30°	52658
35°	38139
40°	23880
45°	13656
50°	7110
55°	3984
60°	2531
65°	1512
70°	1114
75°	475
80°	707
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 13656 cd/sqm

TEST NUMBER: P1500370

CATALOG NUMBER: LD4C08D010 EU4089050 4LBMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	62.5	9.1
10°-20°	164.0	23.9
20°-30°	210.7	30.8
30°-40°	158.5	23.1
40°-50°	63.7	9.3
50°-60°	18.1	2.6
60°-70°	5.7	0.8
70°-80°	1.6	0.2
80°-90°	0.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	437.2	63.8
0°-40°	595.7	87.0
0°-60°	677.5	98.9
0°-90°	685.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	685.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	679	
5°	667	62
15°	585	164
25°	465	211
35°	254	159
45°	79	64
55°	19	18
65°	5	6
75°	1	2
85°	0	0
90°	0	

TEST NUMBER: P1500370

CATALOG NUMBER: LD4C08D010 EU4089050 4LBMH

CANDELA DISTRIBUTION (FULL):

	0°
0°	679.2
2.5°	675.1
5°	666.8
7.5°	651.3
10°	631.6
12.5°	607.9
15°	585.2
17.5°	559.3
20°	531.4
22.5°	501.4
25°	465.2
27.5°	421.8
30°	371.2
32.5°	314.3
35°	254.3
37.5°	198.5
40°	148.9
42.5°	109.6
45°	78.6
47.5°	53.8
50°	37.2
52.5°	25.9
55°	18.6
57.5°	13.4
60°	10.3
62.5°	7.2
65°	5.2
67.5°	4.1
70°	3.1
72.5°	2.1
75°	1.0
77.5°	1.0
80°	1.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)