

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P856905

Luminaire Tested: **LD4C15D010 EU4159027 4LBHYH**

Issue Date: 10/18/2023



Test Information

Test Method: LM-79-08
Report Number: P856905
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2105-247-7)
Test Lab: INNOVATION CENTER
Issue Date: 10/18/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD4C15D010 EU4159027 4LBHYH
Description: 4 INCH 1500 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 2700K, 90CRI LEDS
AND 4LCHYP TRIM WITH MW FINISH
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 901.4 lumens
Efficiency: N/A
Efficacy: 57.1 lumens/watt
Spacing Criteria (0/90/45): 0.59 / 0.59 / 0.59
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 15.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P856905

CATALOG NUMBER: LD4C15D010 EU4159027 4LBHYH

Luminous Intensity Polar Plot





TEST NUMBER: P856905

CATALOG NUMBER: LD4C15D010 EU4159027 4LBHYH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	115	112	110	108	112	110	108	107	106	105	103		103	101	100		99
2	110	106	103	100	108	105	102	99	102	99	97		99	97	95		96
3	106	101	97	94	105	100	96	93	97	94	92		95	93	91		93
4	103	97	92	89	101	96	92	88	94	90	87		92	89	86		90
5	99	92	88	84	97	92	87	84	90	86	83		88	85	83		87
6	95	89	84	81	94	88	83	80	86	83	80		85	82	79		84
7	92	85	80	77	91	84	80	77	83	79	76		82	79	76		81
8	89	82	77	74	88	81	77	74	80	76	73		79	76	73		78
9	86	79	74	71	85	78	74	71	77	73	71		77	73	70		76
10	83	76	71	68	83	76	71	68	75	71	68		74	70	68		73

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	289959
5°	282286
10°	244919
15°	188975
20°	131679
25°	69404
30°	19392
35°	8579
40°	4282
45°	2224
50°	956
55°	129
60°	0
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P856905

CATALOG NUMBER: LD4C15D010 EU4159027 4LBHYH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	207.7	23.0
10°-20°	406.2	45.1
20°-30°	234.8	26.0
30°-40°	41.2	4.6
40°-50°	10.5	1.2
50°-60°	1.1	0.1
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	848.7	94.1
0°-40°	889.8	98.7
0°-60°	901.4	100.0
0°-90°	901.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	901.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2360	
5°	2289	208
15°	1486	406
25°	512	235
35°	57	41
45°	13	10
55°	1	1
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P856905

CATALOG NUMBER: LD4C15D010 EU4159027 4LBHYH

CANDELA DISTRIBUTION (FULL):

	0°
0°	2360.2
2.5°	2356.2
5°	2289.0
7.5°	2148.4
10°	1963.3
12.5°	1746.6
15°	1485.8
17.5°	1217.3
20°	1007.2
22.5°	756.5
25°	512.0
27.5°	292.9
30°	136.7
32.5°	93.4
35°	57.2
37.5°	38.4
40°	26.7
42.5°	18.3
45°	12.8
47.5°	8.3
50°	5.0
52.5°	2.2
55°	0.6
57.5°	0.0
60°	0.0
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)