

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P856906

Luminaire Tested: **LD4C15D010 EU4159027 4LBMLI**

Issue Date: 7/19/2024



**Test Information**

Test Method: LM-79-08  
Report Number: P856906  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P208178)  
Test Lab: INNOVATION CENTER  
Issue Date: 7/19/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LD4C15D010 EU4159027 4LBMLI  
Description: 4 INCH 1500 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 2700K, 90CRI LEDS  
AND 4LBM TRIM WITH LI FINISH  
Light Source: -  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1394.0 lumens  
Efficiency: N/A  
Efficacy: 88.2 lumens/watt  
Spacing Criteria (0/90/45): 0.7 / 0.7 / 0.76  
Luminous Opening: Circular (Dia: 0.33' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 15.8  
Input Voltage (V):  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P856906

CATALOG NUMBER: LD4C15D010 EU4159027 4LBMLI

### Luminous Intensity Polar Plot





TEST NUMBER: P856906

CATALOG NUMBER: LD4C15D010 EU4159027 4LBMLI

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	114	111	109	107	111	109	107	105	105	103	102	101	100	99	98	97	96	94			
2	109	104	100	97	107	102	99	96	99	96	94	96	94	92	94	92	90	88			
3	104	98	93	89	102	96	92	89	94	90	87	91	88	86	89	87	85	83			
4	99	92	87	83	97	91	86	82	89	85	81	87	83	80	85	82	79	78			
5	94	87	81	77	93	86	81	77	84	79	76	82	78	75	81	77	75	73			
6	90	82	76	72	89	81	76	72	80	75	71	78	74	71	77	73	70	69			
7	86	77	72	68	85	77	71	68	75	71	67	74	70	67	73	69	67	65			
8	82	73	68	64	81	73	67	64	72	67	64	71	66	63	70	66	63	62			
9	79	70	64	60	78	69	64	60	68	63	60	67	63	60	67	63	60	58			
10	75	66	61	57	74	66	61	57	65	60	57	64	60	57	64	60	57	56			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	269983
5°	265391
10°	243846
15°	204212
20°	163605
25°	131460
30°	97854
35°	55911
40°	26237
45°	11137
50°	3555
55°	1799
60°	1253
65°	988
70°	611
75°	0
80°	0
85°	0



TEST NUMBER: P856906

CATALOG NUMBER: LD4C15D010 EU4159027 4LBMLI

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	199.0	14.3
10°-20°	444.8	31.9
20°-30°	442.3	31.7
30°-40°	240.9	17.3
40°-50°	55.7	4.0
50°-60°	7.8	0.6
60°-70°	2.9	0.2
70°-80°	0.7	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1086.1	77.9
0°-40°	1326.9	95.2
0°-60°	1390.4	99.7
0°-90°	1394.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1394.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	2198	
5°	2152	199
15°	1606	445
25°	970	442
35°	373	241
45°	64	56
55°	8	8
65°	3	3
75°	0	1
85°	0	0
90°	0	



TEST NUMBER: P856906

CATALOG NUMBER: LD4C15D010 EU4159027 4LBMLI

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	2197.6
2.5°	2192.5
5°	2152.0
7.5°	2069.4
10°	1954.7
12.5°	1786.1
15°	1605.6
17.5°	1426.8
20°	1251.4
22.5°	1108.1
25°	969.8
27.5°	838.2
30°	689.8
32.5°	524.5
35°	372.8
37.5°	251.3
40°	163.6
42.5°	102.9
45°	64.1
47.5°	37.1
50°	18.6
52.5°	10.1
55°	8.4
57.5°	5.1
60°	5.1
62.5°	3.4
65°	3.4
67.5°	1.7
70°	1.7
72.5°	1.7
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG







— 0°-180°







(END OF REPORT)