

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P205608

Luminaire Tested: **LD4B20D010 EU4B10209040 4LBSWMH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P205608
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD4B20D010 EU4B10209040 4LBSWMH1
Description: PORTFOLIO 4 INCH SHALLOW RECESSED DOWNLIGHT
SHALLOW DISTRIBUTION WITH WARM HAZE TRIM
WATTAGE D010TR-21.86W DE010-20.46W D5LT-21.24W DMX-20.89W DL2-22.5W
DL3-21.8 6W DLE-22.46W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1749.3 lumens
Efficiency: N/A
Efficacy: 84.1 lumens/watt
Spacing Criteria (0/90/45): 0.99 / 0.99 / 1.08
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 20.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P205608

CATALOG NUMBER: LD4B20D010 EU4B10209040 4LBSWMH1

Luminous Intensity Polar Plot





TEST NUMBER: P205608

CATALOG NUMBER: LD4B20D010 EU4B10209040 4LBSWMH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	108	105	102	109	106	103	101	102	100	97		98	96	94		95
2	104	98	92	88	102	96	91	87	92	88	85		89	86	83		86
3	96	88	82	76	94	87	81	76	84	79	74		81	77	73		79
4	90	80	73	67	88	79	72	67	76	70	66		74	69	65		72
5	83	73	65	59	82	72	64	59	70	63	59		68	62	58		66
6	78	66	59	53	76	65	58	53	64	57	53		62	57	52		61
7	73	61	53	48	71	60	53	48	59	52	48		57	52	47		56
8	68	56	49	44	67	56	48	43	54	48	43		53	47	43		52
9	64	52	45	40	63	52	45	40	50	44	40		49	44	39		49
10	60	48	41	37	59	48	41	37	47	41	36		46	40	36		45

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P205608

CATALOG NUMBER: LD4B20D010 EU4B10209040 4LBSWMH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	102.5	5.9
10°-20°	271.6	15.5
20°-30°	364.7	20.8
30°-40°	373.3	21.3
40°-50°	323.1	18.5
50°-60°	214.9	12.3
60°-70°	88.3	5.0
70°-80°	10.5	0.6
80°-90°	0.4	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	738.7	42.2
0°-40°	1112.1	63.6
0°-60°	1650.1	94.3
0°-90°	1749.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1749.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1109	
5°	1092	102
15°	970	272
25°	796	365
35°	596	373
45°	421	323
55°	238	215
65°	87	88
75°	5	11
85°	0	0
90°	0	



TEST NUMBER: P205608

CATALOG NUMBER: LD4B20D010 EU4B10209040 4LBSWMH1

CANDELA DISTRIBUTION (FULL):

0°	
0°	1108.7
2.5°	1106.4
5°	1091.5
7.5°	1068.6
10°	1037.6
12.5°	1003.2
15°	970.0
17.5°	927.6
20°	886.3
22.5°	842.7
25°	795.7
27.5°	745.3
30°	694.8
32.5°	644.4
35°	596.2
37.5°	550.4
40°	506.8
42.5°	463.2
45°	420.8
47.5°	376.1
50°	330.2
52.5°	284.3
55°	238.5
57.5°	198.4
60°	157.1
62.5°	119.2
65°	87.1
67.5°	57.3
70°	33.3
72.5°	16.1
75°	4.6
77.5°	2.3
80°	1.1
82.5°	1.1
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)