

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P206238

Luminaire Tested: **LD4B30D010 EU4B30508035 4LBPSMW1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P206238
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD4B30D010 EU4B30508035 4LBPSMW1
Description: PORTFOLIO 4 INCH SHALLOW RECESSED DOWNLIGHT
SHALLOW DISTRIBUTION WITH PLASTIC MATTE WHITE TRIM
WATTAGE D010TR-27.4W DE010-27.95W D5LT-27.65W DMX-27.73W DL2-29.56W
DL3-29.67W DLE-29.73W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3188.5 lumens
Efficiency: N/A
Efficacy: 113.9 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.24 / 1.34
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 28
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P206238

CATALOG NUMBER: LD4B30D010 EU4B30508035 4LBPSMW1

Luminous Intensity Polar Plot





TEST NUMBER: P206238

CATALOG NUMBER: LD4B30D010 EU4B30508035 4LBPSMW1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	110	106	102	99	107	104	100	97	99	97	94	96	93	91	92	90	88	86		
2	101	93	87	82	98	92	86	81	88	83	79	85	81	77	82	79	76	74		
3	93	83	75	69	90	81	74	69	78	72	67	76	70	66	73	69	65	63		
4	85	74	66	59	83	72	65	59	70	63	58	68	62	57	66	61	56	54		
5	78	66	58	51	76	65	57	51	63	56	51	61	55	50	59	54	49	47		
6	73	60	51	45	71	59	51	45	57	50	44	55	49	44	54	48	44	42		
7	67	54	46	40	66	54	46	40	52	45	40	51	44	39	49	43	39	37		
8	63	50	41	36	61	49	41	36	48	41	35	46	40	35	45	39	35	33		
9	59	46	38	32	57	45	37	32	44	37	32	43	36	32	42	36	32	30		
10	55	42	34	29	54	42	34	29	41	34	29	40	33	29	39	33	29	27		

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P206238

CATALOG NUMBER: LD4B30D010 EU4B30508035 4LBPSMW1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	121.7	3.8
10°-20°	347.0	10.9
20°-30°	522.5	16.4
30°-40°	621.8	19.5
40°-50°	620.6	19.5
50°-60°	504.7	15.8
60°-70°	310.5	9.7
70°-80°	120.3	3.8
80°-90°	19.3	0.6
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	991.2	31.1
0°-40°	1613.0	50.6
0°-60°	2738.4	85.9
0°-90°	3188.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3188.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1285	
5°	1281	122
15°	1232	347
25°	1137	523
35°	996	622
45°	807	621
55°	565	505
65°	312	311
75°	110	120
85°	15	19
90°	0	



TEST NUMBER: P206238

CATALOG NUMBER: LD4B30D010 EU4B30508035 4LBPSMW1

CANDELA DISTRIBUTION (FULL):

0°	
0°	1284.6
2.5°	1286.5
5°	1280.9
7.5°	1273.3
10°	1263.9
12.5°	1246.9
15°	1231.7
17.5°	1209.1
20°	1184.5
22.5°	1161.8
25°	1137.3
27.5°	1103.3
30°	1069.3
32.5°	1037.2
35°	995.6
37.5°	950.3
40°	908.7
42.5°	857.7
45°	806.7
47.5°	751.9
50°	693.3
52.5°	632.9
55°	564.9
57.5°	498.7
60°	434.5
62.5°	372.2
65°	311.7
67.5°	255.0
70°	202.1
72.5°	153.0
75°	109.6
77.5°	71.8
80°	43.5
82.5°	26.4
85°	15.1
87.5°	7.6
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)