

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P856769

Luminaire Tested: **LX4C10D010 EX4C109040 4LBMH**

Issue Date: 2/8/2022

**Test Information**

Test Method: LM-79-08  
Report Number: P856769  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P206636)  
Test Lab: INNOVATION CENTER  
Issue Date: 2/8/2022  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LX4C10D010 EX4C109040 4LBMH  
Description: 4 INCH 1000 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 4000K, 90CRI LEDS  
AND 4LBM TRIM WITH H FINISH  
Light Source: -  
Ballast/Driver:

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 770.0 lumens  
Efficiency: N/A  
Efficacy: 78.6 lumens/watt  
Spacing Criteria (0/90/45): 1.18 / 1.18 / 1.13  
Luminous Opening: Circular (Dia: 0.33' x H: 0')  
CIE Type: Direct

Input Watts (W): 9.8  
Input Voltage (V):  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P856769

CATALOG NUMBER: LX4C10D010 EX4C109040 4LBMH

### Luminous Intensity Polar Plot





TEST NUMBER: P856769

CATALOG NUMBER: LX4C10D010 EX4C109040 4LBMH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	112	109	106	104	110	107	104	102	103	101	99	99	97	96	96	94	93	91			
2	105	100	95	91	103	98	93	90	95	91	88	91	88	86	89	86	84	82			
3	99	91	85	80	97	90	84	80	87	82	78	84	80	77	82	79	76	74			
4	92	83	77	72	90	82	76	71	80	75	70	78	73	70	76	72	69	67			
5	87	77	70	65	85	76	69	64	74	68	64	72	67	63	70	66	62	61			
6	81	71	64	58	80	70	63	58	68	62	58	67	61	57	65	61	57	55			
7	76	65	58	53	75	65	58	53	63	57	53	62	56	52	61	56	52	50			
8	72	60	53	49	70	60	53	49	59	53	48	58	52	48	57	52	48	46			
9	68	56	49	45	66	56	49	45	55	49	44	54	48	44	53	48	44	43			
10	64	52	46	41	63	52	46	41	51	45	41	50	45	41	49	44	41	39			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	60972
5°	61205
10°	61389
15°	61393
20°	61055
25°	59630
30°	55736
35°	48262
40°	37704
45°	27051
50°	17564
55°	10517
60°	6167
65°	3953
70°	2622
75°	1994
80°	1486
85°	0



TEST NUMBER: P856769

CATALOG NUMBER: LX4C10D010 EX4C109040 4LBMH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	47.3	6.1
10°-20°	136.2	17.7
20°-30°	201.0	26.1
30°-40°	198.3	25.8
40°-50°	121.4	15.8
50°-60°	46.5	6.0
60°-70°	14.6	1.9
70°-80°	4.3	0.6
80°-90°	0.6	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	384.4	49.9
0°-40°	582.7	75.7
0°-60°	750.6	97.5
0°-90°	770.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	770.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	496	
5°	496	47
15°	483	136
25°	440	201
35°	322	198
45°	156	121
55°	49	47
65°	14	15
75°	4	4
85°	0	1
90°	0	



TEST NUMBER: P856769

CATALOG NUMBER: LX4C10D010 EX4C109040 4LBMH

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	496.3
2.5°	497.4
5°	496.3
7.5°	495.3
10°	492.1
12.5°	487.9
15°	482.7
17.5°	476.4
20°	467.0
22.5°	456.6
25°	439.9
27.5°	419.0
30°	392.9
32.5°	360.5
35°	321.8
37.5°	279.0
40°	235.1
42.5°	194.3
45°	155.7
47.5°	121.2
50°	91.9
52.5°	67.9
55°	49.1
57.5°	34.5
60°	25.1
62.5°	18.8
65°	13.6
67.5°	10.5
70°	7.3
72.5°	5.2
75°	4.2
77.5°	2.1
80°	2.1
82.5°	1.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG







— 0°-180°







(END OF REPORT)