

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P856953

Luminaire Tested: **LX4C15D010 EU4159035 4LBHYLI**

Issue Date: 7/20/2023



Test Information

Test Method: LM-79-08
Report Number: P856953
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2301-896-1)
Test Lab: INNOVATION CENTER
Issue Date: 7/20/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LX4C15D010 EU4159035 4LBHYLI
Description: 4 INCH 1500 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 3500K, 90CRI LEDS
AND 4LBHYP TRIM WITH LI FINISH
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1237.0 lumens
Efficiency: N/A
Efficacy: 78.3 lumens/watt
Spacing Criteria (0/90/45): 0.52 / 0.52 / 0.52
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 15.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P856953

CATALOG NUMBER: LX4C15D010 EU4159035 4LBHYLI

Luminous Intensity Polar Plot





TEST NUMBER: P856953

CATALOG NUMBER: LX4C15D010 EU4159035 4LBHYLI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	115	113	111	109	112	110	109	107	106	105	104		103	102	101		99
2	111	107	104	101	109	105	102	100	102	100	98		99	97	96		97
3	107	102	98	95	105	101	97	94	98	95	93		96	93	91		94
4	103	98	93	90	102	96	93	90	94	91	89		93	90	88		91
5	100	94	89	86	98	93	89	86	91	87	85		89	86	84		88
6	97	90	85	82	95	89	85	82	88	84	81		87	83	81		85
7	93	87	82	79	92	86	82	79	85	81	78		84	80	78		83
8	91	83	79	76	90	83	79	76	82	78	75		81	78	75		80
9	88	81	76	73	87	80	76	73	79	76	73		79	75	73		78
10	85	78	74	71	84	78	73	71	77	73	70		76	73	70		76

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	470111
5°	458243
10°	388505
15°	251818
20°	156376
25°	84165
30°	28925
35°	11653
40°	3111
45°	1390
50°	554
55°	236
60°	147
65°	174
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P856953

CATALOG NUMBER: LX4C15D010 EU4159035 4LBHYLI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	335.2	27.1
10°-20°	552.8	44.7
20°-30°	286.6	23.2
30°-40°	54.3	4.4
40°-50°	6.9	0.6
50°-60°	1.0	0.1
60°-70°	0.4	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1174.5	94.9
0°-40°	1228.8	99.3
0°-60°	1236.7	100.0
0°-90°	1237.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1237.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3827	
5°	3716	335
15°	1980	553
25°	621	287
35°	78	54
45°	8	7
55°	1	1
65°	1	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P856953

CATALOG NUMBER: LX4C15D010 EU4159035 4LBHYLI

CANDELA DISTRIBUTION (FULL):

	0°
0°	3826.6
2.5°	3820.3
5°	3715.8
7.5°	3475.9
10°	3114.3
12.5°	2569.9
15°	1979.9
17.5°	1503.5
20°	1196.1
22.5°	891.7
25°	620.9
27.5°	381.6
30°	203.9
32.5°	137.7
35°	77.7
37.5°	33.7
40°	19.4
42.5°	12.6
45°	8.0
47.5°	4.6
50°	2.9
52.5°	1.1
55°	1.1
57.5°	0.6
60°	0.6
62.5°	0.6
65°	0.6
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)