

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P856961

Luminaire Tested: **LX4C15D010 EX4C159035 4LBNLI**

Issue Date: 1/21/2022



Test Information

Test Method: LM-79-08
Report Number: P856961
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P208279)
Test Lab: INNOVATION CENTER
Issue Date: 1/21/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LX4C15D010 EX4C159035 4LBNLI
Description: 4 INCH 1500 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 3500K, 90CRI LEDS
AND 4LBN TRIM WITH LI FINISH
Light Source: -
Ballast/Driver:

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1153.1 lumens
Efficiency: N/A
Efficacy: 73.0 lumens/watt
Spacing Criteria (0/90/45): 0.48 / 0.48 / 0.54
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 15.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P856961

CATALOG NUMBER: LX4C15D010 EX4C159035 4LBNLI

Luminous Intensity Polar Plot





TEST NUMBER: P856961

CATALOG NUMBER: LX4C15D010 EX4C159035 4LBNLI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97
2	109	105	102	99	107	103	100	98	100	98	95	97	95	93	95	93	92
3	105	99	95	92	103	98	94	91	95	92	89	93	90	88	91	89	87
4	101	94	89	86	99	93	88	85	91	87	84	89	86	83	87	84	82
5	96	89	84	80	95	88	84	80	87	82	79	85	81	79	83	80	78
6	92	85	80	76	91	84	79	76	83	78	75	81	78	75	80	77	74
7	89	81	76	72	88	80	75	72	79	75	71	78	74	71	77	73	71
8	85	77	72	68	84	77	72	68	76	71	68	75	71	68	74	70	67
9	82	74	69	65	81	73	68	65	72	68	65	72	68	65	71	67	64
10	79	71	66	62	78	70	65	62	69	65	62	69	65	62	68	64	62

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	364531
5°	328039
10°	254300
15°	184065
20°	127443
25°	92909
30°	67511
35°	39954
40°	16807
45°	5247
50°	688
55°	386
60°	442
65°	523
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P856961

CATALOG NUMBER: LX4C15D010 EX4C159035 4LBNLI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	233.8	20.3
10°-20°	400.3	34.7
20°-30°	318.2	27.6
30°-40°	168.4	14.6
40°-50°	29.0	2.5
50°-60°	2.2	0.2
60°-70°	1.1	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	952.3	82.6
0°-40°	1120.7	97.2
0°-60°	1152.0	99.9
0°-90°	1153.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1153.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2967	
5°	2660	234
15°	1447	400
25°	685	318
35°	266	168
45°	30	29
55°	2	2
65°	2	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P856961

CATALOG NUMBER: LX4C15D010 EX4C159035 4LBNLI

CANDELA DISTRIBUTION (FULL):

	0°
0°	2967.2
2.5°	2890.8
5°	2660.0
7.5°	2358.1
10°	2038.5
12.5°	1729.5
15°	1447.2
17.5°	1184.4
20°	974.8
22.5°	815.0
25°	685.4
27.5°	580.7
30°	475.9
32.5°	369.3
35°	266.4
37.5°	175.8
40°	104.8
42.5°	60.4
45°	30.2
47.5°	10.7
50°	3.6
52.5°	3.6
55°	1.8
57.5°	1.8
60°	1.8
62.5°	1.8
65°	1.8
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)