

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P1500431

Luminaire Tested: LD4C65D010 EU4659027 4LBMH

Issue Date: 2/8/2022

Test Information

Test Method: LM-79-2019
Report Number: P1500431
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P207151)
Test Lab: INNOVATION CENTER
Issue Date: 2/8/2022
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4C65D010 EU4659027 4LBMH
Description: 4 INCH 6500 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 2700K, 90CRI LEDS AND 4LBM TRIM FINISH
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4825.0 lumens
Efficiency: N/A
Efficacy: 66.6 lumens/watt
Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.93
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 72.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1500431

CATALOG NUMBER: LD4C65D010 EU4659027 4LBMH

Luminous Intensity Polar Plot



TEST NUMBER: P1500431

CATALOG NUMBER: LD4C65D010 EU4659027 4LBMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	108	105	111	108	106	104	104	102	100		100	99	97		97
2	107	102	98	94	105	100	96	93	97	94	91		94	91	89		91
3	101	94	89	85	99	93	88	84	90	86	83		88	84	82		86
4	96	88	82	77	94	86	81	77	84	80	76		82	78	75		80
5	90	82	75	71	89	81	75	70	79	74	70		77	73	69		75
6	86	76	70	65	84	75	69	65	74	68	64		72	68	64		71
7	81	71	65	60	80	70	64	60	69	64	60		68	63	59		67
8	77	67	60	56	75	66	60	56	65	59	56		64	59	55		63
9	73	63	56	52	72	62	56	52	61	56	52		60	55	52		59
10	69	59	53	49	68	59	53	49	58	52	49		57	52	48		56

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	587768
5°	579235
10°	555032
15°	524228
20°	489339
25°	444196
30°	370862
35°	268683
40°	168184
45°	96131
50°	50132
55°	28080
60°	17912
65°	10581
70°	7866
75°	3465
80°	5165
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 96131 cd/sqm

TEST NUMBER: P1500431

CATALOG NUMBER: LD4C65D010 EU4659027 4LBMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	440.2	9.1
10°-20°	1154.9	23.9
20°-30°	1484.3	30.8
30°-40°	1116.7	23.1
40°-50°	448.5	9.3
50°-60°	127.5	2.6
60°-70°	40.4	0.8
70°-80°	11.5	0.2
80°-90°	1.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3079.4	63.8
0°-40°	4196.2	87.0
0°-60°	4772.1	98.9
0°-90°	4825.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4825.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4784	
5°	4697	440
15°	4122	1155
25°	3277	1484
35°	1792	1117
45°	553	448
55°	131	127
65°	36	40
75°	7	12
85°	0	1
90°	0	

TEST NUMBER: P1500431

CATALOG NUMBER: LD4C65D010 EU4659027 4LBMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	4784.3
2.5°	4755.1
5°	4696.9
7.5°	4587.6
10°	4449.2
12.5°	4281.9
15°	4121.7
17.5°	3939.6
20°	3742.9
22.5°	3531.9
25°	3276.9
27.5°	2971.0
30°	2614.3
32.5°	2213.7
35°	1791.5
37.5°	1398.1
40°	1048.7
42.5°	771.9
45°	553.3
47.5°	378.8
50°	262.3
52.5°	182.1
55°	131.1
57.5°	94.7
60°	72.9
62.5°	51.0
65°	36.4
67.5°	29.1
70°	21.9
72.5°	14.6
75°	7.3
77.5°	7.3
80°	7.3
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)